

# SELOS · GROUND BLOCKS WITH SCREW CONNECTION

## WKN 35 SL

- Ground block with screw connection for mounting on TS 35
- Nominal cross section 35 mm<sup>2</sup>
- Ex e I/II Ⓜ II 2GD IM2  
Follow the EX installation instructions on page 160
- Enclosed design



Description	Type	Part No.	Std. Pack
Ground block	green/yellow WKN 35 SL	57.535.9055.0	20
<b>GENERAL DATA</b>			
Width / length / height, incl. TS 7.5	16 mm / 63 mm / 68 mm		
Wire strip length	20 mm		
Approvals			
<b>TECHNICAL DATA</b>			
	<b>IEC</b>	<b>UL</b>	<b>CSA</b>
	EN 60 947-7-2		
Cross section fine-stranded	10 – 35 mm <sup>2</sup>		
Cross section solid/stranded	10 – 50 mm <sup>2</sup>		
Cross section, AWG	10 – 2		
Rated current	600 V		
Rated voltage	800 V		
Rated impulse voltage	8 kV		
Pollution degree	3		

## WKN 70 SL

- Ground block with screw connection for mounting on TS 35
- Nominal cross section 70 mm<sup>2</sup>
- Ex e I/II Ⓜ II 2GD IM2  
Follow the EX installation instructions on page 160
- Enclosed design



Description	Type	Part No.	Std. Pack
Ground block	green/yellow WKN 70 SL	57.570.9055.0	20
<b>GENERAL DATA</b>			
Width / length / height, incl. TS 7.5	24 mm / 75 mm / 81 mm		
Wire strip length	24 mm		
Approvals			
<b>TECHNICAL DATA</b>			
	<b>IEC</b>	<b>UL</b>	<b>CSA</b>
	EN 60 947-7-2		
Cross section fine-stranded	10 – 70 mm <sup>2</sup>		
Cross section solid/stranded	16 – 95 mm <sup>2</sup>		
Cross section, AWG	6 – 2/0		
Rated current	600 V		
Rated voltage	800 V		
Rated impulse voltage	8 kV		
Pollution degree	3		