

## WRGO Type

### Examples of model number formation

WRGO 6 - 300 H - 20Z

1 2 3 4 5

- 1 Part No.    2 Roller Size    3 Length of Race rail  
 4 Accuracy : Normal(No symbol), High(H), Precision(P)  
 5 The number of Roller

\* Please inquire us for your specially required dimensions & applicaton



Part No.	Max. Stroke	D	No. of Roller Z	Dimensions					
				L	A	B	C	M×P	N
WRGO 6100	56	6	7	100	30	15	14.4	1×50	25
WRGO 6150	96		10	150				2×50	
WRGO 6200	136		13	200				3×50	
WRGO 6250	156		17	250				4×50	
WRGO 6300	196		20	300				5×50	
WRGO 6350	216		24	350				6×50	
WRGO 6400	256		27	400				7×50	
WRGO 6450	276		31	450				8×50	
WRGO 6500	316		34	500				9×50	
WRGO 6550	336		38	550				10×50	
WRGO 6600	376		41	600				11×50	
WRGO 9200	118	9	10	200	40	20	19.2	1×100	50
WRGO 9300	178		15	300				2×100	
WRGO 9400	238		20	400				3×100	
WRGO 9500	298		25	500				4×100	
WRGO 9600	359		30	600				5×100	
WRGO 9700	418		35	700				6×100	
WRGO 9800	478		40	800				7×100	
WRGO 9900	538		45	900				8×100	
WRGO 91000	598		50	1000				9×100	
WRGO 91100	658		55	1100				10×100	
WRGO 91200	718		60	1200				11×100	

Note 1) 1Set = 4 Race rail + 2 Roller cages + 8 Stoppers.

Note 2) Basic load ratings are based on 1 set.