

常に新しい研磨面

CARTRIDGE ROLL

軸付カートリッジロール

- 摩耗しても次の新しい面が出てくる為、常に新しい砥粒面で研磨できます。
- 細部の研磨やバリ取りに適しています。



■ ストレート型



φ3mm

φ6mm



サイズ Size (mm) 外径×幅×軸径	粒度 Grit 品番 NO.									入数 Pack	MAX min ⁻¹	Price ¥ (1本単価)
	#60	#80	#100	#120	#150	#180	#240	#320	#400			
6×20×3	RS6204	RS6205	RS6206	RS6207	RS6208	RS6209	RS62010	RS62011	RS62012	10本	20,000	220
10×20×3	RS1034	RS1035	RS1036	RS1037	RS1038	RS1039	RS10310	RS10311	RS10312			
10×20×6	RS1064	RS1065	RS1066	RS1067	RS1068	RS1069	RS10610	RS10611	RS10612			260
10×35×6	RS10354	RS10355	RS10356	RS10357	RS10358	RS10359	RS103510	RS103511	RS103512			
15×25×6	RS15254	RS15255	RS15256	RS15257	RS15258	RS15259	RS152510	RS152511	RS152512			350
16×35×6	RS16354	RS16355	RS16356	RS16357	RS16358	RS16359	RS163510	RS163511	RS163512			
20×25×6	RS20254	RS20255	RS20256	RS20257	RS20258	RS20259	RS202510	RS202511	RS202512			380
20×35×6	RS20354	RS20355	RS20356	RS20357	RS20358	RS20359	RS203510	RS203511	RS203512			
25×35×6	RS25354	RS25355	RS25356	RS25357	RS25358	RS25359	RS253510	RS253511	RS253512			490
25×40×6	RS25404	RS25405	RS25406	RS25407	RS25408	RS25409	RS254010	RS254011	RS254012			

■ テーパー型



φ3mm

φ6mm



サイズ Size (mm) 外径×幅×軸径	粒度 Grit 品番 NO.									入数 Pack	MAX min ⁻¹	Price ¥ (1本単価)
	#60	#80	#100	#120	#150	#180	#240	#320	#400			
6×20×3	RT6204	RT6205	RT6206	RT6207	RT6208	RT6209	RT62010	RT62011	RT62012	10本	20,000	240
10×20×3	RT1034	RT1035	RT1036	RT1037	RT1038	RT1039	RT10310	RT10311	RT10312			
10×20×6	RT1064	RT1065	RT1066	RT1067	RT1068	RT1069	RT10610	RT10611	RT10612			280
10×35×6	RT10354	RT10355	RT10356	RT10357	RT10358	RT10359	RT103510	RT103511	RT103512			
15×25×6	RT15254	RT15255	RT15256	RT15257	RT15258	RT15259	RT152510	RT152511	RT152512			370
16×35×6	RT16354	RT16355	RT16356	RT16357	RT16358	RT16359	RT163510	RT163511	RT163512			
20×25×6	RT20254	RT20255	RT20256	RT20257	RT20258	RT20259	RT202510	RT202511	RT202512			410
20×35×6	RT20354	RT20355	RT20356	RT20357	RT20358	RT20359	RT203510	RT203511	RT203512			
25×35×6	RT25354	RT25355	RT25356	RT25357	RT25358	RT25359	RT253510	RT253511	RT253512			540
25×40×6	RT25404	RT25405	RT25406	RT25407	RT25408	RT25409	RT254010	RT254011	RT254012			