




油圧用210kgf/cm²管フランジ
210 kgf/cm² SLIP-ON WELDING PIPE FLANGE FOR HYD.

LSA
(PIPE FLANGES)

JIS B2291



LSA

UNIT : mm

NOM. SIZE		A ₁	B	A	C	d	d ₁	d ₂	e	d ₃	f	r	h	d ₄	BOLT d ₄	O RING
(A)	(B)															
15	1/2	63.0	36.0	54.0	40.0	16.0	30.0	22.2	11.0	32.0	3.5	5.0	20.0	11.0	M10	G25
20	3/4	70.0	40.0	58.0	45.0	20.0	35.0	27.7	12.0	38.0	4.0	5.0	22.5	11.0	M10	G30
25	1	82.0	48.0	68.0	50.0	25.0	40.0	34.5	14.0	45.0	4.0	5.0	25.0	13.0	M12	G35
32	1-1/4	92.0	56.0	76.0	63.0	31.5	45.0	43.2	16.0	56.0	6.0	5.0	31.5	13.0	M12	G40
40	1-1/2	110.0	65.0	92.0	71.0	37.5	55.0	49.1	18.0	63.0	7.0	5.0	35.5	18.0	M16	G50
50	2	125.0	73.0	100.0	85.0	47.5	65.0	61.1	20.0	75.0	7.0	5.0	42.5	18.0	M16	G60
65	2-1/2	150.0	92.0	128.0	106.0	60.0	80.0	77.1	22.0	95.0	9.5	6.0	53.0	22.0	M20	G75
80	3	170.0	103.0	140.0	118.0	71.0	90.0	90.0	25.0	108.0	11.0	6.0	59.0	24.0	M20	G85

特記： 1. Oリングは JIS B2401
REMARKS : 1. O-RING IS JIS B2401

ヤマト特殊鋼株式会社
YAMATO SPECIAL STEEL CO., LTD.

Sheet No. JF-4