




油圧用210kgf/cm<sup>2</sup>管フランジ  
210 kgf/cm<sup>2</sup> SLIP-ON WELDING PIPE FLANGE FOR HYD.

SHA (PIPE FLANGES)  
SHB (PIPE FLANGES)

JIS B2291



UNIT : mm

NOM. SIZE		A	B	C	d	d <sub>1</sub>	d <sub>2</sub>	e	d <sub>3</sub>	d <sub>4</sub>	f	r	BOLT d <sub>4</sub>	O-RING
(A)	(B)													
15	1/2	63.0	40.0	22.0	16.0	30.0	22.2	11.0	32.0	11.0	3.5	5.0	M10×55	G25
20	3/4	68.0	45.0	22.0	20.0	35.0	27.7	12.0	38.0	11.0	4.0	5.0	M10×55	G30
25	1	80.0	53.0	28.0	25.0	40.0	34.5	14.0	45.0	13.0	4.0	5.0	M12×70	G35
32	1-1/4	90.0	63.0	28.0	31.5	45.0	43.2	16.0	56.0	13.0	6.0	5.0	M12×70	G40
40	1-1/2	100.0	70.0	36.0	37.5	55.0	49.1	18.0	63.0	18.0	7.0	5.0	M16×90	G50
50	2	112.0	80.0	36.0	47.5	65.0	61.1	20.0	75.0	18.0	7.0	5.0	M16×90	G60
65	2-1/2	140.0	100.0	45.0	60.0	80.0	77.1	22.0	95.0	22.0	9.5	6.0	M20×115	G75
80	3	155.0	112.0	45.0	71.0	90.0	90.0	25.0	108.0	24.0	11.0	6.0	M20×115	G85

特記： 1. Oリングは JIS B2401  
REMARKS : 1. O-RING IS JIS B2401  
2. SHA+SHB+O-RING+BOLT&NUT=SHF

ヤマト特殊鋼株式会社  
YAMATO SPECIAL STEEL CO., LTD.

Sheet No. JF-1