

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Accessory Hooks / Sliding Hooks

Accessory Hook - J-Shaped **HFCFJ** (20 pcs./pkg.)

Type	Caster	Hook
HFCFJ	Polyamide	SUS304

RoHS 10

20 pcs. per pkg.

Part Number		Allowable Load (kgf)	Unit Price	Volume Discount Rate
Type	No.			
HFCFJ	5 (For HFS5)	1.8	1 ~ 9 pkg(s).	10~100
	6 (For HFS6)			
	8 (For HFS8 (-45))			

When using No. 8 for HFS8-45, the fit becomes slightly firmer.

Accessory Hook - U-Shaped **HFCFU** (20 pcs./pkg.)

Type	Caster	Hooks
HFCFU	Polyamide	SUS304

RoHS 10

20 pcs. per pkg.

Part Number		Allowable Load (kgf)	Unit Price	Volume Discount Rate
Type	No.			
HFCFU	5 (For HFS5)	1.8	1 ~ 9 pkg(s).	10~100
	6 (For HFS6)			
	8 (For HFS8 (-45))			

When using No. 8 for HFS8-45, the fit becomes slightly firmer.

Accessory Hooks - Clip Type **HFCFK** (20 pcs./pkg.)

Type	Caster	Shaft, Spring	
HFCFK	Polyamide	Material	Surface Treatment
		SWC	Trivalent Chromate

RoHS 10

20 pcs. per pkg.

Part Number		Allowable Load (kgf)	Unit Price	Volume Discount Rate
Type	No.			
HFCFK	5 (For HFS5)	0.5	1 ~ 9 pkg(s).	10~100
	6 (For HFS6)			
	8 (For HFS8 (-45))			

When using No. 8 for HFS8-45, the fit becomes slightly firmer.

Example

Mounting Turns 90 deg.

Sliding Hook **HFCFS** (2 pcs./set)

Material: Polyacetal (White)

There are 2pcs. of sliding hooks in 1 set.

Part Number		Applicable Extrusion (Series)	Allowable Load (kgf)	Unit Price	Volume Discount Rate
Type	No.				
HFCFS	6	HFS6	1.0	1 ~ 9 set(s).	10~100
	8				

1 set has 2 pcs. of sliding hooks.

Example **Features** Post-assembly fitting is possible.

- Insert a sliding hook into the slot while noting for the arrow direction.
- Slightly tilt the sliding hook and move it in the slot to the direction of the arrow.
- Insert a protrusion of the sliding hook into the hole to unite the 2 parts.

Ordering Example

Part Number
HFCFJ5
HFCFU6
HFCFK8
HFCFS6