

Hose Clamps

Suitable for connecting Duct Hoses on P. 1327.

⚠ Hose clamp is the product to prevent the hose from falling off. Structurally, clearance may occur at the smallest tightening torque.

Standard

HOSBS

Hex Socket
7 mm

Material: SUS304

RoHS 10

Ordering Example
Part Number
HOSBS13N

Part Number		Hose O.D. Tightening Range (mm)	L	T	E	Tightening Torque (N · m)	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-50
Type	No.							
HOSBS	9N	9.5-12	19	0.7	9.5	3.5		
	13N	13-20						
	16N	16-22						
	19N	18-25						
	22N	22-30						
	25N	25-35						
	28N	30-40						
	31N	35-50	24	0.8	12	6.1		
	38N	40-55						
	44N	45-60						
	50N	55-70						
	60N	60-80						
	70N	70-90						
	83N	85-100						
	95N	90-120						
	104N	100-125						
127N	130-150							
146N	130-160							
149N	150-180	33			6.9			
175N	170-200							
200N	190-230							

⚠ For orders larger than indicated quantity, please check with WOS.

Spiral

HOSBB

Material: SUS304

RoHS 10

Part Number		Hose O.D. Tightening Range (mm)	L	E	Tightening Torque (N · m)	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-30
Type	No.						
HOSBB	30	30-37	30.5	15	5		
	32	32-42					
	47	47-57					
	61	61-71					
	71	71-81					
	86	86-96					
	90	90-110					

⚠ For orders larger than indicated quantity, please check with WOS.

Hand Tightening

HOSBH

Material: SPCC
Surface Treatment: Trivalent Chromate

RoHS 10

Part Number		Hose O.D. Tightening Range (mm)	L	T	E	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-30
Type	No.						
HOSBH	15	15-22	32	0.5	13		
	18	18-28					
	20	20-34					
	25	25-40					
	40	40-55					

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example
Part Number
HOSBH18

With Safety Cover

Type	Material			
	Clamp	Housing	Screw	Caps
HOABS (Semi Stainless Steel)	SUS430	SUS430	Steel (Zinc Plating)	PE
HOASU (All Stainless Steel)	SUS304	SUS304	SUS304	PE

Material: SUS304

RoHS 10

Ordering Example
Part Number
HOABS13

Part Number		Hose O.D. Tightening Range (mm)	L	T	E	Tightening Torque (N · m)	HOABS		HOASU		
Type	No.						Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-30	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-30	
HOABS HOASU	8	8-12	21.5	0.7	9	3.5					
	10	10-15									
	11	11-17									
	13	13-20									
	16	16-22									
	18	18-25									
	22	22-30	27	0.8	13	5					
	25	25-35									
	27	27-40									
	30	30-45									
	35	35-50									
	40	40-55									
	45	45-60									
	55	55-70									

⚠ For orders larger than indicated quantity, please check with WOS.