

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Balances

B Thermometers and Hygrometers

C Data-Loggers and Recorders

D Water and Soil Analysis

E Air and Gas Analysis

F Natural Environment Analysis

G Electrical Measuring Equipment

H Physical Property Measuring Equipment

I Microscopes

J Fiber Scopes and Loupes

K Lasers / Optical Equipment

L Measuring Tools

## Digital Microscopes

### COMPACT HANDY MICROSCOPE (For iPhone only)

Order No.	Model No.	Specification	JPY	Ref.No
3-6397-01	NINE X40	Magnification/10x~40x	¥ 6,300	064770
3-6397-02	NINE X80	Magnification/20x~80x	¥ 8,500	064770
3-6397-11	5,5S CASE	Case for iPhone5/5s	¥ 1,980	064770
3-6397-12	6,6S CASE	Case for iPhone6/6s	¥ 1,980	064770
3-6397-13	6+,6S+ CASE	Case for iPhone6+/6s+	¥ 1,980	064770


※ Smartphone is not supplied.  
 ※ Dedicated case is necessary to connect microscope to smartphone.

#### Feature

- Provides microscope functions when connected to smartphone.
- User can work with microscope even in dark place by using built-in light of smartphone.
- Capable of saving still and moving images in real time.
- This product can be used by downloading smartphone application.

#### Specification

- Focal Length : NINE X40/8mm, NINE X80/2mm
- Dimensions : 22×15×10mm
- Visual Field : NINE X40/φ 6mm, NINE X80/φ 3mm



NINE X40



NINE X80



6.6S CASE



Mounting Example

**PICK UP**

**NEW**

### DIGITAL MICROSCOPE

CN

Order No.	Model No.	Type	Dimensions (mm)	JPY	Ref.No
3-6350-01	DX-012B	PC Connection	φ32×115	¥ 12,100	064770
3-6350-02	DX-012T	TV Connection	φ32×104	¥ 12,800	064770

#### Feature

- Captures both still and moving images.

#### Specification

- Magnification : 20x~200x ● Light Source : White LED×8
- Interface : DX-012B/USB2.0, DX-012T/Video Terminal
- Accessories : Metal Stand
- Sensor : Color CMOS Sensor/1/3 inch
- Frame Rate : 30fps (max)
- Resolution : 1600×1280 pixels (2 million pixels)
- Applicable OS : Windows®2000/XP/Vista®/7 (DX-012B only)
- Weight : 380g



DX-012T

DX-012B

200 million pixels

**PICK UP**

**NEW**

### DIGITAL MICROSCOPE (With Wi-Fi Function)

Order No.	Model No.	Dimensions (mm)	Weight (g)	JPY	Ref.No
3-5142-01	hidemiconpro2	154×44	129	¥ 38,000	064770

#### Specification

- Sensor : 1/3.2" 3 million pixel CMOS sensor
- Magnification : 10~230x ● Focal Length : 0~50mm
- Video Resolution : 1920×1080, 1280×720, 640×480
- Static Image Resolution : 3M, 5M, 8M, 12M
- Available Wi-Fi range : approx.20m ● Communication Speed : 150Mbps
- Power Supply : Rechargeable (use USB-AC charger via. mini USB cable)
- Charging Time : approx.2 hours ● Battery Usable Time : approx.3hours
- Light Source : LED Light×6 (adjustable intensity)
- Applicable OS : Windows Vista®, Windows®7/8/8.1, Mac OS X 10.6 or greater, iOS 5.0 or greater, Andorid 2.2 or greater

#### Accessories

- Calibration Ruler ● Quick Guide ● CD-ROM
- Power Supply Adapter ● USB Cable ● Stand



300 million pixels

Use Example

#### Feature

- Possible to used to view or store videos and photos by connecting to smartphone, tablet PC or PC via. Wi-Fi or USB.
- Ensures stable image capturing when retained to accessory stand.
- Allows Measuring of distances and angles when used with supplied software.

### HANDY TYPE MICROSCOPE

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
3-5143-01	handymicon4	103×28×130	¥ 23,200	064770

※ Micro SD card is separately sold.

#### Specification

- Magnification : Optical/250x (max.), Digital/4x (max.)
- Resolution : Photo/4032×3024 pixels (max.), Video/640×480 pixels (max.)
- LCD : 3 inches ● Light Source : LED Light×8
- Image Sensor : 5 million pixel COMS Sensor
- Recording Media : Micro SD Card (SDHC) Max.32GB
- Power Supply : Rechargeable Battery (Included), AC Adapter (Included)
- Battery Usable Time : approx.90minutes ● Weight : 300g

#### Accessories

- Video cable (composite) ● USB Cable
- Power Feed Dedicated USB Cable ● USB Charger ● Battery×1
- Strap ● Cleaning Cloth ● Dedicated Porch ● Dedicated Stand



500 million pixels

Stand Example

#### Feature

- Capable of storing videos and photos in micro SD card (sold separately).
- Allows image capturing in handheld mode in addition to fixed mode using the accessory stand.

Please check the related product of this page.

▶ P.662

Handy Fiberscope

