

# 品揃え

国土交通省 公共建築工事標準仕様書 適合  
 JIS規格ねじ込み式可鍛鑄鉄製管継手JIS B 2301 適合  
 日本消防設備安全センター認定品 (PJ-163号)

## BRT

呼び(B)		品名	三方径違いチー	
呼び(B)	型番	型番	BRT	
1/2	1/2	3/4	●	
		1/2	●	
3/4	1/2	3/4	●	
		1	●	
	3/4	1 1/4	●	
		1	●	
1	1/2	1/2	●	
		1	●	
	3/4	1/2	●	
		3/4	●	
	1	1	●	
		1 1/4	●	
	1	1 1/2	●	
		2	※ ●	
1 1/4	3/4	3/4	●	
		1 1/4	●	
	1	1/2	●	
		3/4	●	
		1	●	
		1 1/4	●	
	1 1/2	1 1/2	※ ●	
		2	※ ●	
	1 1/4	1 1/2	●	
		2	●	
1 1/2	3/4	3/4	※ ●	
		1 1/2	●	
	1	1	●	
		1 1/4	●	
		1 1/2	●	
		2	※ ●	
	1 1/2	1 1/4	1/2	●
			3/4	●
		1	1	●
			1 1/4	●
1 1/2	1 1/2	●		
	2	※ ●		
1 1/2	2	●		
	2 1/2	※ ●		

呼び(B)		品名	三方径違いチー	
呼び(B)	型番	型番	BRT	
2	3/4	2	●	
		1	1	※ ●
			1 1/4	※ ●
			1 1/2	※ ●
			2	●
2 1/2	1 1/4	1	※ ●	
		1 1/4	●	
		1 1/2	●	
		2	●	
	2 1/2	2 1/2	※ ●	
		1 1/2	●	
	2 1/2	1 1/4	●	
		1 1/2	●	
	2 1/2	2	●	
		2 1/2	※ ●	
3	2 1/2	2 1/2	●	
		3	●	
	2 1/2	2	※ ●	
		2 1/2	※ ●	
	2 1/2	2	●	
		3	●	
	2 1/2	2	※ ●	
		3	※ ●	
	3	2 1/2	●	
		2 1/2	※ ●	

## BRCr

呼び		品名	四方径違いクロス	
呼び	型番	型番	BRCr	
1	1	3/4	●	
		1	※ ●	
1 1/4	1	3/4	※ ●	
		1	※ ●	
	1 1/4	3/4	●	
		1	●	
1 1/2	1	3/4	※ ●	
		1	※ ●	
		1	※ ●	
		1	※ ●	
	1 1/4	3/4	※ ●	
		1	※ ●	
	1 1/2	3/4	●	
		1	●	
	2	1 1/4	1	※ ●
			3/4	※ ●
1 1/2		1	※ ●	
		1	※ ●	
2		3/4	●	
		1	●	
2		1 1/4	※ ●	
		1 1/4	※ ●	
2		1 1/2	●	
		1 1/2	●	
2 1/2	2	1	※ ●	
		1	●	
	2 1/2	1	●	
		2	●	
3	3	2	●	

上記一覧表以外の品種については、別途ご相談ください。

※ 印は、(一財)日本消防設備安全センター認定品(JIS規格外品)で、認識証票が貼付されています。

