





ライニング鋼管接続用



■ コア継手



■ PCコア継手



呼び (B)	品種 略号	エルボ	45°エルボ	チー	ソケット	プラグ	ユニオン	ニップル	クロスオーバー	合フランジ 合F	
		L	45°L	T	S	P	U	Ni	OS	5kF	10kF
1/2		●	●	●	●	●	○	○		○	○
3/4		●	●	●	●	●	○	○	○	○	○
1		●	●	●	●	●	○	○		○	○
1 1/4		●	●	●	●	●	○	○		○	○
1 1/2		●	●	●	●	●	○	○		○	○
2		●	●	●	●	●	○	○		○	○
2 1/2		●	●	●	●	○	○	○		○	○
3		●	●	●	●	●	○	○		○	○
4		●	●	●	●	○	○	○		○	○
5		●	○	○	●	○	○	○		○	○
6		○	○	○	○	○	○	○		○	○

呼び (B)	品種 略号	径違いエルボ	径違いチー	径違いソケット	径違いクロス
		RL	RT	RS	BRCr
3/4 x 1/2		●	●	●	
1 x 3/4		●	●	●	○
1 x 1/2		●	●	●	
1 1/4 x 1		●	●	●	
1 1/4 x 3/4		●	●	●	○
1 1/4 x 1/2			○		
1 1/2 x 1 1/4		●	●	●	
1 1/2 x 1		●	●	●	○
1 1/2 x 3/4		●	●	●	○
1 1/2 x 1/2			○	○	
2 x 1 1/2		●	●	●	
2 x 1 1/4		○	●	●	
2 x 1		●	●	●	○
2 x 3/4		○	●	●	○
2 x 1/2			○		
2 1/2 x 2		●	●	●	
2 1/2 x 1 1/2		○	●	○	
2 1/2 x 1 1/4			○	○	
2 1/2 x 1			●	○	
2 1/2 x 3/4			●	○	○
2 1/2 x 1/2			○		
3 x 2 1/2		●	●	●	
3 x 2		●	●	●	○
3 x 1 1/2		○	●	○	
3 x 1 1/4			●	○	
3 x 1			●	○	
3 x 3/4			●	○	○
3 x 1/2			○		

呼び (B)	品種 略号	径違いエルボ	径違いチー	径違いソケット	径違いクロス
		RL	RT	RS	BRCr
4 x 3		●	●	●	
4 x 2 1/2		○	●	○	
4 x 2		○	●	○	
4 x 1 1/2			●	○	
4 x 1 1/4			●	○	
4 x 1			○	○	
4 x 3/4			○	○	
4 x 1/2			○		
5 x 4			○	●	
5 x 3			○		
5 x 2 1/2			○		
5 x 2			○		
5 x 1 1/2			○		
6 x 5			○	○	
6 x 4			○	○	
6 x 3			○		
6 x 2 1/2			○		

呼び (B)	品種 略号	三方径違いチー	呼び (B)	品種 略号	三方径違いチー
		BRT			BRT
3/4 x 1/2 x 1/2 (枝側)		○	1 1/4 x 1 1/4 x 2 (枝側)		○
3/4 x 1/2 x 3/4 (枝側)		○			
3/4 x 3/4 x 1 (枝側)		○			
3/4 x 3/4 x 1 1/2 (枝側)		○			
1 x 1/2 x 1/2 (枝側)		○			
1 x 3/4 x 1/2 (枝側)		○			
1 x 3/4 x 3/4 (枝側)		○			
1 x 1 x 1 1/4 (枝側)		○			

○印はコア継手のみです。 ●印はPCコア継手もあります。