


스페셜 P



Elesa 표준		주요 치수													흡		핸들			q
코드	사양	D	L	B	d1	d2	d3	d5	f1	h2	l1	l2	l4	R	dh7	h	H	m	R1	q
CE.28502	VAD.80-PXX1 A-10	80	55	13	20	20.5	56	6	M4	3.5	18.5	11.5	13.6	19	10	22.5	-	-	-	205
CE.28552	VAD.100-PXX1 A-10	100	63.5	14	20	20.5	56	6	M4	3.5	18.5	11.5	13.6	19	10	22.5	-	-	-	265
CE.28602	VAD.125-PXX2 A-12	125	65.5	15	32	22.5	76	6	M4	4	19	12	13.1	28.5	12	22.5	-	-	-	450
CE.28652	VAD.160-PXX2 A-14	160	71.5	18	32	25.5	78	6	M4	4	20	13	12.1	28.5	14	23.5	-	-	-	680
CE.28702	VAD.160-PXX5 A-14	160	64	18	32	25.5	120	6	M4	4	20	13	12.1	28.5	14	23.5	-	-	-	760
CE.28512	VAD.80-PXX1 A-10+I	80	55	13	20	20.5	56	6	M4	3.5	18.5	11.5	13.6	19	10	22.5	40	M6	33.5	230
CE.28562	VAD.100-PXX1 A-10+I	100	63.5	14	20	20.5	56	6	M4	3.5	18.5	11.5	13.6	19	10	22.5	50	M6	42.5	300
CE.28612	VAD.125-PXX2 A-12+I	125	65.5	15	32	22.5	76	6	M4	4	19	12	13.1	28.5	12	22.5	65	M8	54	520
CE.28662	VAD.160-PXX2 A-14+I	160	71.5	18	32	25.5	78	6	M4	4	20	13	12.1	28.5	14	23.5	80	M10	71	760
CE.28712	VAD.160-PXX5 A-14+I	160	64	18	32	25.5	120	6	M4	4	20	13	12.1	28.5	14	23.5	80	M10	71	840

조립 가능한 인디케이터

코드	사양	코드	사양	GA01	GA02	GA05	GA11	GA12	GW12	PA01	PA02	PA05	PA11	PA12	PW12
CE.28501	VAD.80-GXX1 A-10	CE.28511	VAD.80-GXX1 A-10+I	┆			┆								
CE.28551	VAD.100-GXX1 A-10	CE.28561	VAD.100-GXX1 A-10+I	┆			┆								
CE.28601	VAD.125-GXX2 A-12	CE.28611	VAD.125-GXX2 A-12+I		┆			┆	┆						
CE.28651	VAD.160-GXX2 A-14	CE.28661	VAD.160-GXX2 A-14+I		┆			┆	┆						
CE.28701	VAD.160-GXX5 A-14	CE.28711	VAD.160-GXX5 A-14+I			┆									
CE.28721	VAD.200-GXX2 A-18	CE.28726	VAD.200-GXX2 A-18+I		┆			┆	┆						
CE.28731	VAD.250-GXX2 A-22	CE.28736	VAD.250-GXX2 A-22+I		┆			┆	┆						
CE.28502	VAD.80-PXX1 A-10	CE.28512	VAD.80-PXX1 A-10+I							┆			┆		
CE.28552	VAD.100-PXX1 A-10	CE.28562	VAD.100-PXX1 A-10+I							┆			┆		
CE.28602	VAD.125-PXX2 A-12	CE.28612	VAD.125-PXX2 A-12+I								┆			┆	┆
CE.28652	VAD.160-PXX2 A-14	CE.28662	VAD.160-PXX2 A-14+I								┆			┆	┆
CE.28702	VAD.160-PXX5 A-14	CE.28712	VAD.160-PXX5 A-14+I									┆			

해당 인디케이터 기술 자료 페이지

298	298	298	299	299	301	304	304	304	304	305	305	306
-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----