





(単位: mm)

ゲージユニオン (Gネジ)




呼び径D	A	D1	B	B1	L	L1	L2	L3	品番
3.2	G1/8	5.5	10	14	29	22.5	13	16	F900-G-3.2AF
3.2	G1/4	5.5	10	17	32	25.5	13	19	F900-G-3.2BF
6.35	G1/8	5.5	14	14	31	24	15	16	F900-G-6.35AF
6.35	G1/4	5.5	14	17	34	27	15	19	F900-G-6.35BF
6.35	G3/8	5.5	14	21	36	29	15	21	F900-G-6.35CF
6.35	G1/2	5.5	14	26	40	33	15	25	F900-G-6.35DF
9.52	G1/8	5.5	17	17	33	25	17.5	15.5	F900-G-9.52AF
9.52	G1/4	5.5	17	17	36	28	17.5	18.5	F900-G-9.52BF
9.52	G3/8	5.5	17	21	38	30	17.5	20.5	F900-G-9.52CF
9.52	G1/2	5.5	17	26	42	34	17.5	24.5	F900-G-9.52DF
12.7	G1/8	5.5	22	22	37	26	24	13	F900-G-12.7AF
12.7	G1/4	5.5	22	22	40	29	24	16	F900-G-12.7BF
12.7	G3/8	5.5	22	22	42	31	24	18	F900-G-12.7CF
12.7	G1/2	5.5	22	26	46	35	24	22	F900-G-12.7DF

ゲージユニオン (Rcネジ)



呼び径D	A	D1	B	B1	L	L1	L2	L3	品番
3.2	Rc1/8	2.7	10	14	29	22.5	13	16	F900-G-3.2A
3.2	Rc1/4	2.7	10	17	32	25.5	13	19	F900-G-3.2B
6.35	Rc1/8	5	14	14	31	24	15	16	F900-G-6.35A
6.35	Rc1/4	5	14	17	34	27	15	19	F900-G-6.35B
6.35	Rc3/8	5	14	21	36	29	15	21	F900-G-6.35C
6.35	Rc1/2	5	14	26	40	33	15	25	F900-G-6.35D
9.52	Rc1/8	7	17	17	33	25	17.5	15.5	F900-G-9.52A
9.52	Rc1/4	7.5	17	17	36	28	17.5	18.5	F900-G-9.52B
9.52	Rc3/8	7.5	17	21	38	30	17.5	20.5	F900-G-9.52C
9.52	Rc1/2	7.5	17	26	42	34	17.5	24.5	F900-G-9.52D
12.7	Rc1/8	7	22	22	37	26	24	13	F900-G-12.7A
12.7	Rc1/4	10	22	22	40	29	24	16	F900-G-12.7B
12.7	Rc3/8	10	22	22	42	31	24	18	F900-G-12.7C
12.7	Rc1/2	10	22	26	46	35	24	22	F900-G-12.7D

ゲージユニオン (NPTネジ)



呼び径D	A	D1	B	B1	L	L1	L2	L3	品番
3.2	1/8NPT	2.7	10	14	29	22.5	13	16	F900-G-3.2AN
3.2	1/4NPT	2.7	10	17	32	25.5	13	19	F900-G-3.2BN
6.35	1/8NPT	5	14	14	31	24	15	16	F900-G-6.35AN
6.35	1/4NPT	5	14	17	34	27	15	19	F900-G-6.35BN
6.35	3/8NPT	5	14	21	36	29	15	21	F900-G-6.35CN
6.35	1/2NPT	5	14	26	40	33	15	25	F900-G-6.35DN
9.52	1/8NPT	7	17	17	33	25	17.5	15.5	F900-G-9.52AN
9.52	1/4NPT	7.5	17	17	36	28	17.5	18.5	F900-G-9.52BN
9.52	3/8NPT	7.5	17	21	38	30	17.5	20.5	F900-G-9.52CN
9.52	1/2NPT	7.5	17	26	42	34	17.5	24.5	F900-G-9.52DN
12.7	1/8NPT	7	22	22	37	26	24	13	F900-G-12.7AN
12.7	1/4NPT	10	22	22	40	29	24	16	F900-G-12.7BN
12.7	3/8NPT	10	22	22	42	31	24	18	F900-G-12.7CN
12.7	1/2NPT	10	22	26	46	35	24	22	F900-G-12.7DN

最新のカタログは、"<http://www.fujikin.co.jp/go/c70201>"よりダウンロードできます。