


テークアップ形ユニット

UCT
円筒穴(止めねじ付き)
d 12 ~ (60) mm



軸径 (mm)	寸 法 (mm)															ユニット 呼び番号	適用 軸受箱 (普通品)
	A	A ₁	A ₂	H	H ₁	H ₂	L	L ₁	L ₂	L ₃	N	N ₁	N ₂	B	S		
12	32	12	21	89	76	51	94	61	10	51	19	16	32	31	12.7	UCT201	T204
15	32	12	21	89	76	51	94	61	10	51	19	16	32	31	12.7	UCT202	T204
17	32	12	21	89	76	51	94	61	10	51	19	16	32	31	12.7	UCT203	T204
20	32	12	21	89	76	51	94	61	10	51	19	16	32	31	12.7	UCT204	T204
25	32	12	24	89	76	51	97	62	10	51	19	16	32	34.1	14.3	UCT205	T205
	37	12	28	102	89	56	113	70	10	57	22	16	37	38.1	15.9	UCTX05	TX05
	36	12	26	89	80	62	122	76	12	65	26	16	36	38	15	UCT305	T305
30	37	12	28	102	89	56	113	70	10	57	22	16	37	38.1	15.9	UCT206	T206
	37	12	30	102	89	64	129	78	13	64	22	16	37	42.9	17.5	UCTX06	TX06
	41	16	28	100	90	70	137	85	14	74	28	18	41	43	17	UCT306	T306
35	37	12	30	102	89	64	129	78	13	64	22	16	37	42.9	17.5	UCT207	T207
	49	16	36	114	102	83	144	88	15	83	29	19	49	49.2	19	UCTX07	TX07
	45	16	32	111	100	75	150	94	15	80	30	20	45	48	19	UCT307	T307
40	49	16	33	114	102	83	144	88	16	83	29	19	49	49.2	19	UCT208	T208
	49	16	36	117	102	83	144	87	15	83	29	19	49	49.2	19	UCTX08	TX08
	50	18	34	124	112	83	162	100	17	89	32	22	50	52	19	UCT308	T308
45	49	16	35	117	102	83	144	87	16	83	29	19	49	49.2	19	UCT209	T209
	49	16	38	117	102	83	149	90	16	86	29	19	49	51.6	19	UCTX09	TX09
	55	18	38	138	125	90	178	110	18	97	34	24	55	57	22	UCT309	T309
50	49	16	37	117	102	83	149	90	16	86	29	19	49	51.6	19	UCT210	T210
	64	22	42	146	130	102	171	106	19	95	35	25	64	55.6	22.2	UCTX10	TX10
	61	20	40	151	140	98	191	117	20	106	37	27	61	61	22	UCT310	T310
55	64	22	38	146	130	102	171	106	19	95	35	25	64	55.6	22.2	UCT211	T211
	64	22	44	146	130	102	194	119	19	102	35	32	64	65.1	25.4	UCTX11	TX11
	66	22	44	163	150	105	207	127	21	115	39	29	66	66	25	UCT311	T311
60	64	22	42	146	130	102	194	119	19	102	35	32	64	65.1	25.4	UCT212	T212

備考) 1. ユニット呼び番号及びカバー付きユニットの呼び番号には、内径番号の後にはめあい記号が付きます。(55頁の表 10.5 参照)
2. 適用するグリースニップルの呼びを次に示します。
B-1/4-28UNF...201~210, X05~X09, 305~308
B-R1/8...211~217, X10~X17, 309~328

3. T204JE3、T205JE3 (鋳鉄カバー付き軸受箱) の形状と L_c寸法を次に示します。



T204JE3 L_c = 97 mm
T205JE3 L_c = 102 mm