

Industrial Hose

For Machine Tools, Plastic Molding Machine, or Facilities

EIGHTLOCK® S/B EIGHTNIPPLE S/B Spring Guards




E-TB

PRESSURE HOSE

- E-TB is good at flexibility and shows great resistance to high pressure.
- Great transparency makes it easier to confirm fluid flow.

EIGHTRON®



Model Number	I.D. × O.D. mm	Working Pressure (MPa)		Minimum Bend Radius (20°C) mm	Temperature Range °C	Standard Length M	Weight g/m	Package		Color
		at 20°C	at 60°C					Film Wrapping	Paper Bobbin	
E-TB-4	4 × 9			30		100	65	○	○	Clear Blue
E-TB-6	6 × 11			40		100	85	○	○	
E-TB-8	8 × 13.5			55		100	120	○	○	
E-TB-9	9 × 15		0 ~ 0.7	65		100	145	○	○	
E-TB-10	10 × 16			70		100	155	○	○	
E-TB-12	12 × 18	0 ~ 1.0		85		100	180	○	○	
E-TB-15	15 × 22			105	0 ~ 60	100	260	○	—	
E-TB-19	19 × 26			135		50	315	○	○	
E-TB-21.5	21.5 × 29		0 ~ 0.6	155		50	365	○	—	
E-TB-25	25 × 33			175		50	460	○	—	
E-TB-32	32 × 41			225		50	650	○	—	
E-TB-38	38 × 48	0 ~ 0.5	0 ~ 0.35	265		50	850	○	—	
E-TB-50	50 × 62	0 ~ 0.3	0 ~ 0.2	350		40	1,330	○	—	
E-TB-63	63 × 80			440		20	2,400	○	—	
E-TB-75	75 × 92	0 ~ 0.2	0 ~ 0.1	525		20	2,800	○	—	

EIGHTLOCK® S/B EIGHTNIPPLE S/B Spring Guards




E-STB

Oil-Proof PRESSURE HOSE

- E-STB has excellent oil-proof performance.
- Hoses are suitable for various situations such as industrial oil tubes, machine tools, and plastic molding machine.

EIGHTRON®



Model Number	I.D. × O.D. mm	Working Pressure (MPa)		Minimum Bend Radius (20°C) mm	Temperature Range °C	Standard Length M	Weight g/m	Package Type	Color
		at 20°C	at 60°C						
E-STB-6	6 × 11			40		100	85		Clear Green
E-STB-8	8 × 13.5			55		100	120		
E-STB-9	9 × 15		0 ~ 0.7	65		100	145		
E-STB-12	12 × 18			85		100	180		
E-STB-15	15 × 22	0 ~ 1.0		105	0 ~ 60	50	260	Film Wrapping	
E-STB-19	19 × 26			135		50	315		
E-STB-21.5	21.5 × 29		0 ~ 0.6	155		50	365		
E-STB-25	25 × 33			175		50	460		
E-STB-32	32 × 41			225		40	650		
E-STB-38	38 × 48	0 ~ 0.5	0 ~ 0.35	265		40	850		
E-STB-50	50 × 62	0 ~ 0.3	0 ~ 0.2	350		40	1,330		

DATA Weight Change after Soaking into the Oil

