


## DY

### VENTED DRAIN WYE

Multiple uses of the size 14 & 16



LONG TYPE newly (lined-up) added



**Purpose**

- Joins 2 drain hoses.

**Features**


- Integral air vent promotes drainage flow.

Item No.	Compliant drain hose	Pcs/Pkg
DY-1416	DH-14/16, DHQ-14/16	100
DY-1416L	DH-14/16, DHQ-14/16	100

\*Material ... PE

## DS

### DRAIN HOSE SADDLE



**Features**



- Attractive, compact, quick fitting.
- Weather resistant.
- Ivory color matches DRAIN HOSE.
- Appearance matches SLIMDUCT SD/NSD/MD.

Item No.	Compliant drain hose	A	B	C	D	Pcs/Pkg
DS-14	DH-14 • DHQ-14	26.6	18	39.3	23.3	500
DS-16	DH-16 • DHQ-16	28.6	20	41.3	25.3	500

\*Material ... PP

## DC

### DRAIN CAP



**Features**

- Prevents insects from entering DRAIN HOSE.
- One-touch mounting to O.D. of DRAIN HOSE.
- Fits both 14mm & 16mm hose.

Item No.	Compliant drain hose	Pcs/Pkg
DC-1416	DRAIN HOSE φ14 • 16	50sets (2 pcs/set)

\*Material ... PP

## NDA

### DRAIN HOSE ADAPTOR



**Features**

- NDA easily connects drain hose to NEO drain pipe coupler or VP/VE pipe coupler.
- Only drain hose can be removed from coupler.
- Transparent body permits easy check for drain hose connection.

Item No.	Compliant drain hose	Pcs/Pkg
NDA-1416	DH-14/16, DHQ-14/16	20


\*Material ... Acrylic resin

Compliant Neo drain pipe coupler	Compliant PVC pipe coupler
For O.D. 26mm, O.D. 32mm	For VP (O.D. 26mm), VP(O.D. 32mm)

Use exclusively with INABA DENKO Drain Hose

## DHB

### MINI INLINE TRAP



**Purpose**

- In an airtight home, pressure difference between indoors and outdoors may cause air backflow and result in noise. DHB Trap promotes condensate flow thus prevents noise and deters insects from entering DRAIN HOSE.

**Features**

- Transparent body permits easy inspection.
- Weather resistant plastic requires no protective tapes.
- Easy to clean.
- Accepts DHQ 14 & DHQ 16 without adaptor.

Item No.	Compliant drain hose	Pcs/Pkg
DHB-1416	DHQ-14 • DHQ-16	50

\*Material ... Acrylic resin