

Nameplates		All dimensions in mm.			
Shape	Legend	Material	Part No.	Ordering No.	Package Quantity
	<div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>NSA</p> <p>1.2 mm thick</p> </div> <div style="width: 15%;"> <p>Blank</p> </div> <div style="width: 15%;"> <p>Aluminum (black) (Legend: white)</p> </div> <div style="width: 10%;"> <p>NSA-0</p> </div> <div style="width: 10%;"> <p>NSA-0</p> </div> <div style="width: 10%;"> <p>1</p> </div> </div> <hr/> <div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>With legend</p> </div> <div style="width: 15%;"> <p>NSA-□</p> </div> <div style="width: 10%;"> <p>NSA-□</p> </div> <div style="width: 10%;"> <p>NSA-□PN10</p> </div> <div style="width: 10%;"> <p>1</p> </div> <div style="width: 10%;"> <p>10</p> </div> </div>				
<div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>NSALO</p> <p>1.2 mm thick</p> </div> <div style="width: 15%;"> <p>Blank</p> </div> <div style="width: 15%;"> <p>Aluminum (black)</p> </div> <div style="width: 10%;"> <p>NSALO</p> </div> <div style="width: 10%;"> <p>NSALO</p> </div> <div style="width: 10%;"> <p>1</p> </div> </div> <hr/> <div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>NSALO</p> </div> <div style="width: 10%;"> <p>NSALOPN10</p> </div> <div style="width: 10%;"> <p>10</p> </div> </div>					
<div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>NFSO</p> <p>1.2 mm thick</p> </div> <div style="width: 15%;"> <p>Blank</p> </div> <div style="width: 15%;"> <p>Stainless Steel</p> </div> <div style="width: 10%;"> <p>NFSO</p> </div> <div style="width: 10%;"> <p>NFSO</p> </div> <div style="width: 10%;"> <p>1</p> </div> </div> <hr/> <div style="display: flex; justify-content: space-between;"> <div style="width: 20%;"> <p>NFSO</p> </div> <div style="width: 10%;"> <p>NFSOPN10</p> </div> <div style="width: 10%;"> <p>10</p> </div> </div>					

• Specify a legend code in place of □ in the Ordering No.

Legends

Code	Legend
0	(blank)
1	ON
2	OFF
3	START
4	STOP
31	OFF ON
35	HAND AUTO
53	HAND OFF AUTO

Engraving Area on Nameplates

Shape	Engraving Area (mm)		Max. No. of Lines	No. of Letters per Line
	Height	Width		
<p>Standard (NSA/NFSO)</p>	4	31	1	17
<p>Mushroom (NSALO)</p>	8	31	2	17

- The above example is when the letter is 3 mm tall.
- Engraving must be made within 1.5 mm from the sides.