

K-Timing Pulley Flange

Flange for XL/L/H/S5M/S8M/T5/T10 (SPCC Steel/Thickness 1.6 & 2.3-type)

m: SPCC Steel

Flange No.	Outer Diameter Do	φd	T	Pulley No. and No. of Teeth						¥	
				XL	L	H	S5M	S8M	T5		T10
KTF-165136	51	36	1.6		15		30			15	
KTF-165441	54	41			16		32				
KTF-165539	55	39			17					16	
KTF-165741	57	41			18	14	34,36			17,18	
KTF-166141	61	41									
KTF-166550	65	50			19,20	15				19	
KTF-166950	69	50			21	16	40			20	
KTF-167453	74	53			22,23	17	44			21,22	
KTF-167858	78	58			24	18				23	
KTF-168363	83	63			46,47	25	48		48,49,50	24	
KTF-168666	86	66			48,49,50	26,27	20	50	51,52	25,26	
KTF-169073	90	73			51,52		21		53,54	27	
KTF-169375	93	75			53,54,55	28,29	22		55,56	28	
KTF-169978	99	78			56,57,58,59	30,31	23	60	57,58,59,60	29,30	
KTF-1610584	105	84			60,61,62,63	32	24		61,62,63	31,32	
KTF-1610884	108	84				33	25		64,65		
KTF-1611290	112	90			64,65	34,35	26		66,67	33,34	
KTF-1611590	115	90			66,67,68	36	27		68,69,70	35	
KTF-1611890	118	90			69,70,71	37	28		71,72	36	
KTF-16126100	126	100			72,73,74,75	38,39,40	29,30		73,74,75,76,77	37,38	
KTF-16131101	131	101		76,77,78,79	41,42	31		78,79,80	39,40		
KTF-16136118	136	118		80	43	32		81,82,83	41		
KTF-16138125	138	125		81,82,83	44	33		84,85	42		
KTF-16146128	146	128		84,85,86,87	45,46	34,35		86,87,88,89	43,44		
KTF-16152134	152	134		88,89,90,91	47,48	36		90,91,92	45,46		
KTF-16159141	159	141			49,50	38			47,48		
KTF-16168150	168	150				40					
KTF-235436	54	36	2.3				18				
KTF-235739	57	39					19				
KTF-236040	60	40					20				
KTF-236244	62	44					21				
KTF-236545	65	45					22				
KTF-237050	70	50					24				
KTF-237252	72	52					25				
KTF-237555	75	55					26				
KTF-238060	80	60					28				
KTF-238565	85	65					30				
KTF-239070	90	70					32				
KTF-239575	95	75					34				
KTF-2310080	100	80					36				
KTF-2310585	105	85									
KTF-2311090	110	90					40				
KTF-23121101	121	101					44				
KTF-23131111	131	111					48				
KTF-23136101	136	101									
KTF-23136116	136	116						50			
KTF-23144111	144	111									
KTF-23152121	152	121									
KTF-23161131	161	131									
KTF-23161141	161	141					60				
KTF-23190161	190	161									
KTF-23200164	200	164									
KTF-23208173	208	173									
KTF-23224190	224	190									
KTF-23235200	235	200									
KTF-23260224	260	224									

Semi-F Series
of FITLINK
Roller
Chains
Chain
Accessories
Idlers &
Tensioners
Sprockets
Bushings
O-Rings
Transmission
Accessories
Conveyor Chains/
Sprockets
Chain
Couplings
Resin Halls
Tight Speed/Car
/Transp/Chains
Timing Belts/
Pulleys/Flanges
Shaft Collars
Pinions/Racks/
Miter Gears
Imperfect
Products