



角 型



単位：mm

L X W X H	L X W X H	L X W X H	L X W X H
4 X 3.2 X 0.65	25 X 19 X 4.5	40 X 40 X 15	80 X 80 X 20
4 X 4 X 2	25 X 19 X 5	41.5 X 4 X 3.3	85 X 65 X 0.9
7 X 7 X 4	25.5 X 25.5 X 3	47.5 X 47.5 X 20	90 X 34 X 20
12 X 8 X 2.5	27 X 8.5 X 4	48 X 15 X 5	95 X 95 X 1
12.5 X 8.5 X 4.7	27 X 14.5 X 7	48 X 22 X 10	95 X 95 X 2
13.5 X 5.5 X 2	30 X 6 X 4	50 X 20 X 5	96 X 10 X 3
15 X 10 X 4	30 X 9 X 6	50 X 50 X 12	100 X 15 X 5
15 X 15 X 5	30 X 10 X 5	50 X 50 X 18	100 X 35 X 5
18 X 11.5 X 5	30 X 10 X 10	55 X 4 X 4	100 X 50 X 10
18.5 X 6 X 3	30 X 20 X 5	55 X 30 X 18	100 X 100 X 3
20 X 10 X 4	30 X 30 X 10	58 X 14 X 16	100 X 100 X 5
20 X 10 X 5	34 X 8 X 5	58 X 14 X 19	100 X 100 X 8
20 X 12 X 5	34 X 34 X 10	58 X 14 X 25	100 X 100 X 10
20 X 15 X 7	35 X 15 X 4.5	60 X 30 X 5	110 X 33.5 X 10
20 X 20 X 10	40 X 12 X 6	60 X 30 X 10	150 X 26 X 15
23 X 22 X 8	40 X 12 X 8	63 X 14 X 10	150 X 100 X 15
24 X 10 X 4	40 X 25 X 5	63.5 X 19 X 5	150 X 100 X 20
25 X 6 X 4	40 X 25 X 10	65 X 15 X 25.4	150 X 100 X 25.4
25 X 8 X 5	40 X 40 X 10	68 X 18 X 12	150 X 100 X 40
25 X 15 X 7	40 X 40 X 12	75 X 30 X 25.4	


超ウス型



単位：mm

OD X H
3.8φ X 0.53
4φ X 0.6
5φ X 1
13φ X 1.2
15φ X 1.2
19φ X 1.2
20φ X 1.2

バー型 (角タイプ)





単位：mm

W X H X L
3 X 3 X 7
4 X 10 X 20
6 X 6 X 18
6.3 X 6.8 X 27.5
7 X 7 X 12
9.75 X 9.75 X 25.4

角 型 (穴付)

1穴タイプ




2穴タイプ

L X W X H X (ID)	備 考
8 X 8 X 7 (2.5φ)	
12 X 9 X 5 (3φ)	
20 X 12 X 4 (6φ)	
22 X 16 X 5 (5φ)	
24 X 13.5 X 4.5 (5φ)	
24.6 X 14.7 X 3 (3.3φ)	段穴付
25 X 19 X 4.5 (5φ)	段穴付

単位：mm


L X W X H X (ID)	備 考
30 X 18 X 6 (4.5φ)	
40 X 25 X 5.2 (5φ)	段穴付
40 X 40 X 10 (12φ)	
48 X 22.5 X 10 (5φ X 2)	皿穴2つ付
60 X 30 X 10 (7φ X 2)	2穴タイプ
85 X 65 X 18 (9φ)	

セグメント型 (大型)



4個組み合わせて、
大型のリング磁石として
ご利用できます。

品 番	R X r X W X H	角 度
SEG-20	158 X 85 X 216 X 25.4	90°



単位：mm