




WEB Selection Tool

WEB CAD Download

Miniature Size

SUS Stainless steel



SNZFS

SNZF-TBZ

● Part number specification

SNZFS-M1.7-3



Order in number of packs.
The minimum order quantity is 1 piece. → P.794

- Miniature screws for precision instruments.(JCIS 10 - 70)
- M1.4 - M2.6.
- More compact head than standard flat head machine screws.

● Application

Reducing the size of equipment and devices
Compact precision instruments

● Material/Finish

RoHS Compliant

	SNZF-TBZ	SNZFS
Main	SWCH16A	SUSXM7
Body	Black Trivalent Chromate Treatment	(S.S. grade : A2)

Unit : mm

SNZF-TBZ Steel - Black Trivalent Chromate Treatment		SNZFS Stainless steel		Common dimensions									
Part Number	Mass (g)	Part Number	Mass (g)	M	L						D1	L1	
SNZF-M1.4-TBZ	0.016 - 0.066	SNZFS-M1.4	0.016 - 0.066	M1.4	2	3	4	5	6	8		2	0.45
		SNZFS-M1.6	0.033 - 0.11	M1.6		3	4	5	6	8	10	2.3	0.5
SNZF-M1.7-TBZ	0.027 - 0.13	SNZFS-M1.7	0.04 - 0.13	M1.7	2	3	4	5	6	8	10	2.5	0.5
SNZF-M2-TBZ	0.038 - 0.18	SNZFS-M2	0.056 - 0.18	M2	2	3	4	5	6	8	10	3	0.6
SNZF-M2.6-TBZ	0.1 - 0.27	SNZFS-M2.6	0.1 - 0.27	M2.6		3	4	5	6	8		4	0.8

*1 **SNZF-TBZ** Steel - Black Trivalent Chromate Treatment only is a standard product.

SNZF-TBZ Steel - Trivalent Chromate Treatment

Part Number	Qty per pack*1
SNZF-M1.4-TBZ	50
SNZF-M1.7-TBZ	50
SNZF-M2-TBZ	50
SNZF-M2.6-TBZ	50

*1 The minimum order quantity is 1 piece. → P.794

SNZFS Stainless Steel

Part Number	Qty per pack*1
SNZFS-M1.4	50
SNZFS-M1.6	50
SNZFS-M1.7	50
SNZFS-M2	50
SNZFS-M2.6	50

*1 The minimum order quantity is 1 piece. → P.794

Individual Sales → P.794	Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Modification process for captive use → P.791
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available