


SDP 鉄工用ドリル Drills for Steels



●もっとも広い用途で使用されている汎用ドリルです。

This drill is applied for general purpose.



オーダ方法

SDP 直径

単位 (Unit) : mm

直径 Dc	溝長 ℓ	全長 L	JANコード 4991893	包装 本数
0.2	3	19	046069	2
0.3	3.5	20	046076	2
0.4	5.5	24	046083	2
0.5	7.5	30	046090	2
0.6	8.5	30	046106	2
0.7	10	32	046113	2
0.8	11	34	046120	2
0.9	13	36	046137	2
1.0	18	40	046144	2
1.1	20	42	046151	2
1.2	20	42	046168	2
1.3	22	45	046175	2
1.4	23	48	046182	2
1.5	23	48	046199	2
1.6	25	50	046205	2
1.7	25	50	046212	2
1.8	28	52	046229	2
1.9	28	52	046236	2
2.0	29	55	046243	2
2.1	29	55	046250	2
2.2	33	58	046267	2
2.3	33	58	046274	2
2.4	35	61	046281	2
2.5	35	61	046298	2
2.6	37	64	046304	2
2.7	37	64	046311	2
2.8	39	67	046328	2
2.9	42	71	046335	2
3.0	42	71	046342	2
3.1	42	71	046359	2
3.2	42	71	046366	2
3.3	45	73	046373	2
3.4	45	73	046380	2
3.5	45	73	046397	2
3.6	48	76	046403	2
3.7	48	76	046410	2
3.8	48	76	046427	2
3.9	51	79	046434	2
4.0	54	83	046441	2
4.1	54	83	046458	1
4.2	54	83	046465	1
4.3	54	83	046472	1
4.4	56	86	046489	1
4.5	56	86	046496	1
4.6	56	86	046502	1
4.7	59	89	046519	1
4.8	59	89	046526	1
4.9	62	92	046533	1
5.0	62	92	046540	1

直径 Dc	溝長 ℓ	全長 L	JANコード 4991893	包装 本数
5.1	62	92	046557	1
5.2	64	95	046564	1
5.3	64	95	046571	1
5.4	64	95	046588	1
5.5	64	95	046595	1
5.6	67	98	046601	1
5.7	67	98	046618	1
5.8	67	98	046625	1
5.9	67	98	046632	1
6.0	70	102	046649	1
6.1	70	102	046656	1
6.2	70	102	046663	1
6.3	70	102	046670	1
6.4	73	105	046687	1
6.5	73	105	046694	1
6.6	73	105	046700	1
6.7	73	105	046717	1
6.8	73	105	046724	1
6.9	73	105	046731	1
7.0	73	105	046748	1
7.1	75	108	046755	1
7.2	75	108	046762	1
7.3	75	108	046779	1
7.4	78	111	046786	1
7.5	78	111	046793	1
7.6	78	111	046809	1
7.7	81	114	046816	1
7.8	81	114	046823	1
7.9	81	114	046830	1
8.0	81	114	046847	1
8.1	84	117	046854	1
8.2	84	117	046861	1
8.3	84	117	046878	1
8.4	87	121	046885	1
8.5	87	121	046892	1
8.6	87	121	046908	1
8.7	87	121	046915	1
8.8	89	124	046922	1
8.9	89	124	046939	1
9.0	89	124	046946	1
9.1	89	124	046953	1
9.2	92	127	046960	1
9.3	92	127	046977	1
9.4	92	127	046984	1
9.5	92	127	046991	1
9.6	95	130	047004	1
9.7	95	130	047011	1
9.8	95	130	047028	1
9.9	95	130	047035	1