



TELESCOPING INSPECTION MIRROR



- Body : Stainless steel
- ### FEATURES
- Inspection of hard-to-see locations
 - Body : Brass (IMT-60LR, IMT-80LR : Stainless steel)
 - Mirror : Glass
 - Extendable reach and easy to carry
 - Replacement mirror (Round type 60, oval type 80) also sold separately

DIMENSIONS




Order No.	Model No.	Mirror Shape (mm)	A : Maximum Length (mm)	B : Telescope Length (mm)	C (mm)	Dimensions	Weight	Note
011140	IMT-20R	Round ϕ 20	Approx. 525	Approx. 130~475	10	①	40g	with clip
011150	IMT-30R	Round ϕ 30	Approx. 535	Approx. 130~475	10	①	40g	with clip
011170	IMT-50K	Oval 50×25	Approx. 555	Approx. 130~475	10	①	45g	with clip
011185	IMT-85S	Square 100×85	Approx. 745	Approx. 245~610	13	①	200g	with clip
011186	IMT-100S	Square 100×100	Approx. 745	Approx. 245~610	13	①	200g	with clip
011187	IMT-100R	Round ϕ 100	Approx. 745	Approx. 245~610	13	①	200g	with clip
011181	IMT-80LK	Oval 80×50	Approx. 945	Approx. 160~840	14	②	100g	Long type
011161	IMT-60LR	Round ϕ 60	Approx. 925	Approx. 160~840	14	②	100g	Long type

INSPECTION MIRROR



DIMENSIONS




FEATURES


- For inspection in hard-to-see location
- Body : Steel
- Mirror : Glass
- Mirror firmly held for easy inspection

Order No.	Model No.	Mirror shape (mm)	A (mm)	B (mm)	Weight
011120	IM-20R	Round ϕ 20	Approx. 200	Approx. 145	50g
011130	IM-30R	Round ϕ 30	Approx. 210	Approx. 145	50g
011110	IM-50K	Oval 50×25	Approx. 230	Approx. 145	50g

MAGNIFYING INSPECTION MIRROR WITH TELESCOPING



DIMENSIONS



FEATURES

- For inspection in hard-to-see location
- Body : Brass
- Mirror : Glass
- Extendable reach and easy to carry
- Mirror magnifies objects for better visibility

Order No.	Model No.	Mirror shape (mm)	A:Max Length (mm)	B:Telescope Length (mm)	Magnification	Weight
011195	IMTR-20R	Round ϕ 20	Approx. 525	Approx. 130~475	2	40g
011196	IMTR-30R	Round ϕ 30	Approx. 535	Approx. 130~475	2	40g
011197	IMTR-60R	Round ϕ 60	Approx. 560	Approx. 130~475	1.5	60g
011198	IMTR-50K	Oval 50×25	Approx. 555	Approx. 130~475	2	45g
NEW-011199	IMTR-80K	Oval 80×50	Approx. 575	Approx. 130~475	1.5	60g

STEREO MICROSCOPE

FIBER SCOPE

TECHNO-ENDOSCOPE

CIRCLE SCOPE

MICRO SCOPE

INSPECTION MIRROR

MAGNIFIER