

## CARBIDE TIPPED SCRIBER




Rust prevention▶  
Zerust Film for Steel  
P380



SDH-30

### ● DIMENSIONS



Units: mm

Model No.	A	B	C	D	E	F
SDH-30	75	63	11.7	8	6	5.3
SDH-60	102	70	25	12	10	9

### FEATURES

- Scriber for digital height gauge VH-30D, VH-60D

### MATERIAL

- Stainless steel
- Carbide tipped

Order No.	Model No.	Applicable Height Gauge	Weight
151215	SDH-30	VH-30D	30g
151216	SDH-60	VH-60D	100g

## SCRIBER CLAMP



Rust prevention▶  
Zerust Film for Steel  
P380




VH-30D-C



VH-60D-C

### ● DIMENSIONS



Units: mm

Model No.	A	B	C	D	E
VH-30D-C	20	25	9	6	18
VH-60D-C	22	35	14.5	10	24

### FEATURES

- Scriber clamp for digital height gauge VHS-30D, VHS-60D

### MATERIAL

- Stainless steel

Order No.	Model No.	Applicable Model No.	Weight
151222	VH-30D-C	VH-30D	20g
151223	VH-60D-C	VH-60D	50g

## INDICATOR HOLDER ARM



Rust prevention▶  
Zerust Film for Steel  
P380



ADH-30



ADH-60

### FEATURES

- Dedicated indicator holder arm for VH-30D, VH-60D

### MATERIAL

- Stainless steel

### SPECIFICATIONS

- Mount size:  $\phi 8\text{mm}$  ( $\phi 6\text{mm}$  collet included)
- Arm length: ADH-30...Approx. 75mm  
ADH-60...Approx. 30mm

Order No.	Model No.	Applicable Height Gauge	Weight
151217	ADH-30	VH-30D	35g
151218	ADH-60	VH-60D	20g

## INDICATOR HOLDER



Rust prevention▶  
Zerust Film for Steel  
P380



### FEATURES

- Dedicated indicator holder for VH-30D  
※Indicator holder for VH-60D is VHS-T ⇒ refer to P198

### MATERIAL

- Steel

### SPECIFICATIONS

- Mount size:  $\phi 6\text{mm}$ ,  $\phi 8\text{mm}$ , Dovetail mount
- Arm length: Approx. 60mm

Order No.	Model No.	Applicable Height Gauge	Weight
151214	ADH-30D	VH-30D	45g

CALIPER

SCRIBING CALIPER

DEPTH GAUGE

HEIGHT GAUGE