

Medium Duty Casters

TP6200 Series / Capacity up to 550 Lbs. each



Features

- **Finish:** Bright zinc plating
- **Swivel:** Double ball bearing with hardened raceways for extra strength
- **Rigid:** Welded with heavy duty gauge steel for extra strength
- **Fork Leg Spacing:** 2"
- **Grease Fittings:** Grease hole in lower raceway cup
- **Axle:** 1/2" diameter zerk axle with lock nut

Applications

- Medium Duty Platform Truck
- Bread Racks
- Food Service Equipment
- Warehouse Carts

Caster Options

- TLB: Top Lock Brake



- Rigid



TP6200 Series

Wheel Diameter	Tread Width	Wheel Type	Swivel Number	Rigid Number	Wheel Bearing	Load Capacity	Overall Height	Swivel Radius
4	1-1/2	Fever Hi-Temp Heavy Duty Plastic	TP6240-**-FVR	TP6240R-**-FVR	Roller	400	5-5/16	3-3/8
		Polyurethane / Cast Iron	TP6240-**-HPB	TP6240R-**-HPB	Ball	450		
		Phenolic	TP6240-**-PCI	TP6240R-**-PCI	Roller	450		
		Pro-Tech Polyurethane	TP6240-**-PHN	TP6240R-**-PHN	Roller	450		
		Rubber / Cast Iron	TP6240-**-PHN-HT	TP6240R-**-PHN-HT	Roller	450		
			TP6240-**-PRO	TP6240R-**-PRO	Roller	450		
5	1-1/2	Fever Hi-Temp Heavy Duty Plastic	TP6250-**-FVR	TP6250R-**-FVR	Roller	500	6-5/16	4-1/8
		Polyurethane / Cast Iron	TP6250-**-HPB	TP6250R-**-HPB	Ball	500		
		Phenolic	TP6250-**-PCI	TP6250R-**-PCI	Roller	500		
		Pro-Tech Polyurethane	TP6250-**-PHN	TP6250R-**-PHN	Roller	500		
		Rubber / Cast Iron	TP6250-**-PHN-HT	TP6250R-**-PHN-HT	Roller	500		
			TP6250-**-PRO	TP6250R-**-PRO	Roller	500		
6	1-1/2	Fever Hi-Temp Heavy Duty Plastic	TP6260-**-FVR	TP6260R-**-FVR	Roller	500	7-1/2	4-5/8
		Polyurethane / Cast Iron	TP6260-**-HPB	TP6260R-**-HPB	Ball	500		
		Phenolic	TP6260-**-PCI	TP6260R-**-PCI	Roller	550		
		Polyurethane / Cast Iron	TP6260-**-PHN	TP6260R-**-PHN	Roller	500		
		Rubber / Cast Iron	TP6260-**-PHN-HT	TP6260R-**-PHN-HT	Roller	550		
			TP6260-**-PRO	TP6260R-**-PRO	Roller	450		

Fastenings

TYPE	CODE	SIZE (Inch)	
Top Plate	02	Overall Size	4 x 4-1/2
		Bolt Hole Spacing	2-5/8 x 3-5/8 slotted to 3 x 3
		Attaching Bolt Size	3/8
Threaded Stem	21	5/8 - 11 x 2	

Options

CODE	DESCRIPTION
TLB	Top Lock Brake
TG	Thread Guard

Add Option Code to end of part number.

Wheel Options



RCI

PCI

PRO (RED)

PRO (MAROON)

PHN

FVR-4K7-F

PLX