

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items



### Flat Square Bar Stay (stainless steel)



- Features**
- Made of stainless steel and excellent in corrosion resistance.
- Use**
- Assistance for furniture and others.
  - Equipment casing.
- Materials**
- Stainless Steel (SUS304)
- Origin**
- Japan



TS-48-LR  
(for left and right)



Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Total Length (mm)	Thickness (mm)	Stopper (mm)	Hole Diameter (mm)	Hole Number	SPQ (piece)	Weight (g)
302-2081	TS-46-LR	¥1,324	¥1,430	Left-right multi-use	180	3	2 pieces 4	4 (L washer)	2 (L washer)	10	82
302-2072	TS-48-LR	¥1,398	¥1,510	Left-right multi-use	240	3	2 pieces 4	4 (L washer)	2 (L washer)	10	78

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

### Front Lid Round Bar Slide Stay (steel)





- Features**
- A simple structure to install.
- Use**
- Assistance for furniture and others.
  - Equipment casing.
- Materials**
- Cold Rolled Steel Plate (SPCC)
  - Surface Treatment: Chrome Plated Finishing
- Origin**
- Japan



TS-34-LR  
(for left and right)



TS-35-LR  
(for left and right)



Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Total Length (mm)	Thickness (mm)	Hole Diameter (mm)	Hole Number	SPQ (piece)	Weight (g)
302-2099	TS-34-LR	¥482	¥520	Left-right multi-use	230	5	3.5 (round), 3.3 (L washer)	3 (round), 2 (L washer)	10	54
302-2102	TS-35-LR	¥583	¥630	Left-right multi-use	254	4	3.5 (round), 3.2 (L washer)	3 (round), 2 (L washer)	10	46

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items



### Rotary Stay (stainless steel)



- Features**
- By opening the lid, it becomes stopped state with the rotary function. When closing, the stopped state is released by slightly lifting it.
- Use**
- Made of stainless steel and excellent in corrosion resistance.
  - Assistance for furniture and others.
  - Equipment casing.
- Materials**
- Stainless Steel (SUS304)
- Origin**
- Japan



TS-192-R  
(for right)



Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Total Length (mm)	Thickness (mm)	Hole Diameter (mm)	Hole Number	SPQ (piece)	Weight (g)
302-2056	TS-193-L	¥1,713	¥1,850	For left	150	1.5	4.5	4	10	74
302-2030	TS-192-L	¥1,759	¥1,900	For left	198	1.5	4.5	4	10	85
302-2013	TS-191-L	¥2,120	¥2,290	For left	277	2.0	4.5	4	10	125
302-2064	TS-193-R	¥1,713	¥1,850	For right	150	1.5	4.5	4	10	74
302-2048	TS-192-R	¥1,759	¥1,900	For right	198	1.5	4.5	4	10	85
302-2021	TS-191-R	¥2,120	¥2,290	For right	277	2.0	4.5	4	10	125

Contact us: 0120-509-849 <http://www.orange-book.com/>