


Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

## Magnet Catch (vertical type) RoHS



- Features**
- Simple structure and highly versatile magnetic catch.
- Specs**
- Recommended Flat Head Screw for Receiving Board: 6.2mm
  - Main Body Mounting Hole Dimension: 3.5mm
- Materials**
- **Main Body: Brass**
  - Bracket: Steel
- Accessories**
- Bracket
- Origin**
- China



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
279-5787	TMC-0083D	¥444	¥480	Silver	80	98	20	63


Contact us: 0120-509-849 <http://www.orange-book.com/>

SUGATSUNE **Stock 766 Items**

## Magnet Catch (vertical type) RoHS



- Features**
- Using a neodymium magnet, it has high adsorption compared with same-shaped products.
- Specs**
- Main Body Mounting Hole Dimension: 3.5mm
- Materials**
- **Main Body: Stainless Steel (SUS304)**
- Origin**
- Japan



Order Unit: 1 Piece SUGATSUNE KOGYO Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
497-3682	MC0083-N	¥1,156	¥1,070	Silver	50	137	40	41


Contact us: 03-3851-1122 <http://www.sugatsune.co.jp/>

SUGATSUNE **Stock 766 Items**

## Heat Resistant Magnetic Catch (vertical type) RoHS



- Features**
- Heat resistant specification (approx. 250°C).
  - Made of stainless steel and has excellent corrosion resistance.
- Materials**
- **Cover: Stainless steel (SUS304)**
  - **York: Stainless steel (SUS430)**
- Origin**
- Japan




Order Unit: 1 Piece (Price revision date: May, 2015) SUGATSUNE KOGYO Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
377-0141	MC0083HP-70	¥2,138	¥1,980	Silver	50	70	40	40
377-0133	MC0083HP-140	¥2,765	¥2,560	Silver	50	140	40	40

Contact us: 03-3851-1122 <http://www.sugatsune.co.jp/>



- Features**
- Heat resistant specification (approx. 250°C).
  - Since it is small and does not take much spaces, spaces can be effectively utilized.
  - Made of stainless steel and has excellent corrosion resistance.
- Materials**
- **Cover: Stainless steel (SUS304)**
  - **York: Stainless steel (SUS430)**
- Origin**
- Japan




Order Unit: 1 Piece (Price revision date: May, 2015) SUGATSUNE KOGYO Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
377-0214	MC-YN005HP-20	¥1,134	¥1,050	Silver	39	20	200	11
377-0222	MC-YN005HP-50	¥1,188	¥1,100	Silver	39	50	200	11


Contact us: 03-3851-1122 <http://www.sugatsune.co.jp/>

TRUSCO **Stock 38,650 Items**

## Magnet Catch (embedded type) RoHS



- Features**
- An embedded magnet catch with high durability.
- Specs**
- Embedded type
  - Main Body Mounting Hole Dimension: 5mm
- Materials**
- **Main body: Aluminum**
- Origin**
- Japan



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
300-5216	TSM-16R	¥476	¥515	Silver	80	90	50	52
300-5224	TSM-16S	¥476	¥515	Silver	80	160	50	56


Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Magnet Catch (embedded type) RoHS



- Features**
- Exposure of appearance can be reduced and it is optimum for wooden furnitures, etc.
- Specs**
- Embedded type
  - Body mounting hole dimension: 3.2 x 6.2mm countersunk hole
- Materials**
- **Main Body: ABS Resin**
- Origin**
- Japan



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Adhesion Strength (N)	SPQ (piece)	Weight (g)
300-5194	TSM-131	¥134	¥145	Black	48	30	100	18

Contact us: 0120-509-849 <http://www.orange-book.com/>

Hardware

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers