


Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

Electrical Level



- Features**
- A convenient level for vertical leveling of switch box mounting frame installation
 - 1 single to 3 consecutive scribbling is possible.
 - Made of polycarbonate makes it impact resistance.
 - With magnet.
 - TDL-95T is equipped with an inspection tester (80V to 220V compliant).
- Use**
- Vertical linearity setting of switch box mounting frame.
- Specs**
- Precision: within $\pm 1.5\text{mm/m} = \pm 0.0859^\circ$
 - Sensitivity: $0.5\text{mm/m} = 0.0286^\circ$
- Materials**
- Main Body: Polycarbonate
 - Bubble Tube: Acrylic Plastic (PMMA)
- Origin**
- Japan



TDL-95T (with inspection tester)

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	L x H x Thickness (mm)	Magnet	SPQ (piece)	Weight (g)
478-9261	TDL-95	¥1,731	¥1,870	95 x 50 x 11	1 Location	10	57
478-9270	TDL-95T	¥2,278	¥2,460	95 x 50 x 11	1 Location	10	62

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Slide Type Pocket Level



- Features**
- With a pen clip, it is convenient to carry in a chest pocket.
 - When installing an air conditioner, it can slide according to the horizontal reference surface of the backboard (approx. 230mm).
 - It is made of ABS resin and hard to give damages to a floor when falling.
- Use**
- For horizontal measurement in narrow places or air-conditioning installation.
- Specs**
- Precision: within $\pm 1.5\text{mm/m} = \pm 0.0859^\circ$
 - Sensitivity: $0.5\text{mm/m} = 0.0286^\circ$
- Materials**
- Main Body: ABS Resin
 - Bubble Tube: Acrylic Plastic (PMMA)
- Origin**
- Japan



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	L x H x Thickness (mm)	Magnet	SPQ (piece)	Weight (g)
478-9288	TSPL-230	¥2,037	¥2,200	167 x 18.7 x 18.7	None	10	35

With a magnet Features • With magnet, it sticks to the iron part surface.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	L x H x Thickness (mm)	Magnet	SPQ (piece)	Weight (g)
478-9296	TSPL-230M	¥2,129	¥2,300	167 x 18.7 x 18.7	2 Locations	10	35


Contact us: 0120-509-849 <http://www.orange-book.com/>




When extended

TRUSCO **Stock 38,650 Items**

Pocket Spirit Level



- Features**
- Pocket type with a powerful magnets that is useful for scaffolding work and interior construction.
- Use**
- For horizontal confirmation of narrow measurement site such as the top of the pipe.
- Specs**
- Precision: within $\pm 1.5\text{mm/m} = \pm 0.0859^\circ$
 - Sensitivity: $0.5\text{mm/m} = 0.0286^\circ$
- Materials**
- Main Body: ABS Resin
 - Bubble Tube: Acrylic Plastic (PMMA)
- Origin**
- Japan



For mounting of distribution panel board embedded power outlet

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	L x H x Thickness (mm)	Magnet	SPQ (piece)	Weight (g)
229-7388	PL-13	¥1,786	¥1,930	130 x 47 x 18	1 Location	10	95

Contact us: 0120-509-849 <http://www.orange-book.com/>

SK **Stock 1,103 Items**

Super Magnetic Level

- Features**
- With strong magnet (2-fold compared with our company's products) on the measurement surface.
 - With V-shaped groove on the measurement surface that is convenient for measurement of round-shape items.
- Use**
- For horizontal/vertical level measurement.
- Specs**
- Precision: within $\pm 1.50\text{mm/m} = \pm 0.0859^\circ$
 - Sensitivity: $0.50\text{mm/m} = 0.0286^\circ$
- Materials**
- Body: Plastic
 - Bubble Tube: Acrylic Plastic (PMMA)
- Origin**
- Taiwan



Order Unit: 1 Piece

NIIGATASEIKI Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	L x H x Thickness (mm)	Magnet	SPQ (piece)	Weight (g)
412-1601	ML-100KB	¥1,512	¥1,400	Black	100 x 47 x 20	1 Location	12	80
412-1619	ML-100KW	¥1,512	¥1,400	White	100 x 47 x 20	1 Location	12	80
412-1627	ML-150KB	¥1,944	¥1,800	Black	150 x 47 x 20	1 Location	12	110
412-1635	ML-150KW	¥1,944	¥1,800	White	150 x 47 x 20	1 Location	12	110

Contact us: 0256-31-5660 <http://www.sokuteikougu.com/>

Measuring Tapes

Tape Measures

Road Counters

Line Lasers

Laser Distance Meters

Rotary Lasers

Theodolites

Automatic Levels

Staffs

Levels

Slant Levels

Stud Finders

Plumb Bobs

Ink Lines, Chalk Reels

Construction Writing Tools

Blackboards

Surveying Signs