

# Tape Measures

The number next to the logo mark indicates items in stock for each brand.

TRUSCO **Stock 38,650 Items**

## "Fiberglass Mini Measure"



- Features**
- Made of fiberglass making allowing measurement of curve surface.
  - Lightweight, easy to handle and convenient.
- Specs**
- Standard Tensile Strength: None
- Materials**
- **Tape: Fiber Glass**
- Origin**
- Japan



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
762-1647	TGM15-B	¥658	¥710	1.5	12	0.33	50	28
762-1655	TGM15-P	¥658	¥710	1.5	12	0.33	50	28

Contact us: 0120-509-849 <http://www.orange-book.com/>

MURATEC KDS **Stock 280 Items**

## "Flat Rule"



- Features**
- Optimum flat tape for curved surface measurement.
- Specs**
- JIS Class 1 Equivalent
  - Standard Tensile Strength: None
- Materials**
- **Tape: Steel**
- Origin**
- Malaysia



Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
331-3069	F10-02P	¥843	¥1,250	2	10	0.18	12	70

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>

MURATEC KDS **Stock 280 Items**

## "Diameter Rule"



- Features**
- $\pi$  major which makes you understood the diameter at a glance, by measuring the circumference.
- Specs**
- JIS Class 1 Equivalent
  - Standard Tensile Strength: None
- Materials**
- **Tape: Steel**
- Origin**
- Malaysia



Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
331-3051	F10-02DMP	¥900	¥1,330	2	10	0.18	12	70


Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>

SHINWA **Stock 519 Items**

## "Spring Measure"



- Features**
- The tape is automatically pulled in by pressing the automatic pulling-in button.
- Use**
- For measurement for dress-making or a curved surface.
- Materials**
- **Tape: PVC coating containing glass fiber**
  - Main body/Tape edge part: ABS resin
- Origin**
- China




Order Unit: 1 Piece SHINWA RULES Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
816-4007	71005	¥432	¥560	1.5	8	1.5	10	25

Contact us: 0120-666-899 <http://www.shinwasokutei.co.jp/>

MURATEC KDS **Stock 280 Items**

## "KACLONG"



- Features**
- Compact type.
- Specs**
- Standard Tensile Strength: 20N
- Materials**
- **Tape: Steel**
- Origin**
- Malaysia




Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
000-1635	KL10-10	¥2,429	¥3,600	10	10	0.18	10	190
000-1643	KL10-20	¥3,644	¥5,400	20	10	0.18	10	320
000-1651	KL10-30	¥5,131	¥7,600	30	10	0.18	10	415

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>

MURATEC KDS **Stock 280 Items**

## "Rubber Tough Mick Capsule"



- Features**
- Excellent non-slip rubber touch with excellent hold feeling.
  - Fiberglass tape, chemical resistance and electric insulation that do not break and washable with water.
  - White/yellow two tone double-sided scale. (front: white/2mm scale, back: yellow/5mm scale)
- Specs**
- Standard Tensile Strength: 10N
- Materials**
- **Tape: Glass Fiber**
- Origin**
- Japan



Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
292-0701	GK12-10N	¥1,724	¥2,550	10	12	0.5	10	247
292-0719	GK12-20N	¥2,565	¥3,800	20	12	0.5	10	384
292-0727	GK12-30N	¥3,644	¥5,400	30	12	0.5	10	538

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>