


▶▶▶ The countersunk head tapping screw, see p. 2-477 to 478.

The number next to the logo mark indicates items in stock for each brand.

TRUSCO **Stock 38,650 Items** **Panel Holder**



- Features**
- The panel holder is a standoff that does not require troublesome hole drilling.
 - The panel is mounted by fixing the cap screws to the base metal fittings attached to the wall and fixing the panel by sandwiching the panel itself.
- Specs**
- Countersunk Screw Diameter for Use: 4mm (sold separately)
 - Scratch-prevention packing attached
 - Thickness of Mounting Object: 5 to 8mm
 - Cap Screw: Diameter 23mm x Height 13mm
 - Base Metal Fitting: Diameter 18mm x Height 21mm
- Materials**
- Cap Screw: Brass
 - Base Metal Fitting: Brass (chrome-plated finishing)
 - Scratch-Prevention Packing: PVC
- Origin**
- Japan



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	SPQ (piece)	Weight (g)
855-5759	PH-AA650	¥1,527	¥1,650	Chrome	10	45
855-5760	PH-AA651	¥1,527	¥1,650	Matte Black (coating)	10	45
855-5761	PH-AA652	¥1,527	¥1,650	Matte White (coating)	10	45

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO NAKAYAMA CORPORATION

Hexagon Bolts

Hexagon Socket Head Cap Screws

Hexagon Socket Set Screws

Wing Bolts

Decoration Screws, Nuts

Nuts

Caps for Screw

Washers

Small Screws

Mischiefous Prevention Screws

Drill Screws

Tapping Screws


Wood Screws

Nails

TRUSCO **Stock 38,650 Items** **Metal Fitting for Pictogram Easy Pic**



- Features**
- Troublesome pictogram sign installation becomes easy.
- Specs**
- Countersunk Screw Diameter for Use: 4mm (sold separately)
 - Hole Diameter of Mounting Object: 7mm
 - Thickness of Sandwiched Board: For 5mm
- Materials**
- Brass
 - Surface Treatment: Chrome-Plated Finishing
- Origin**
- Japan



Order Unit: 1 Piece


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Mounting Hole Number (piece)	SPQ (piece)	Weight (g)
855-5758	EP-AA701	¥4,046	¥4,370	1	10	66
855-5757	EP-AA700	¥4,749	¥5,130	2	10	132

Contact us: 0120-509-849 <http://www.orange-book.com/>


TRUSCO NAKAYAMA CORPORATION



TRUSCO **Stock 38,650 Items** **Panel Fix Universal**



PF-AA075 to 083
PF-AA810 to 812



PF-AA800 to 802

- Features**
- Ideal for small decoration that stand out.
- Use**
- A decorative cap for installing mirrors and acrylics onto walls.
 - Menu boards and guide plates in restaurants and beauty salons.
- Specs**
- Countersunk Screw Diameter for Use: 4mm (sold separately)
 - Hole Diameter of Mounting Object: 6mm
 - Brass Washer Attached
- Origin**
- China

Brass (chrome plating)

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter x H (mm)	SPQ (piece)	Weight (g)
855-5678	PF-AA070	¥241	¥260	12 x 7	10	6
855-5679	PF-AA071	¥278	¥300	16 x 7	10	11
855-5680	PF-AA072	¥352	¥380	20 x 7	10	17
855-5681	PF-AA073	¥407	¥440	25 x 7	10	28

Brass (black chrome plating)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter x H (mm)	SPQ (piece)	Weight (g)
855-5682	PF-AA075	¥269	¥290	12 x 7	10	6
855-5683	PF-AA076	¥306	¥330	16 x 7	10	11

Stainless Steel (buffing finishing)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter x H (mm)	SPQ (piece)	Weight (g)
855-5684	PF-AA080	¥454	¥490	12 x 7	10	5
855-5685	PF-AA081	¥528	¥570	16 x 7	10	10
855-5686	PF-AA082	¥685	¥740	20 x 7	10	17
855-5687	PF-AA083	¥787	¥850	25 x 7	10	26

Resin Materials • Polypropylene (PP)
Origin • Japan

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Outer Diameter x H (mm)	Color	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
855-5688	PF-AA800	¥3,082	¥3,330	16 x 6.5	White	50	10	53
855-5689	PF-AA801	¥3,082	¥3,330	16 x 6.5	Black	50	10	53
855-5690	PF-AA802	¥5,091	¥5,500	16 x 6.5	Chrome	50	10	52

All-Stainless Steel Materials • Stainless Steel (SUS304)
Origin • Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter x H (mm)	SPQ (piece)	Weight (g)
855-5691	PF-AA810	¥509	¥550	12 x 7	10	5
855-5692	PF-AA811	¥630	¥680	16 x 7	10	10
855-5693	PF-AA812	¥814	¥880	20 x 7	10	17

Contact us: 0120-509-849 <http://www.orange-book.com/>