

Suspension Brackets (screw fastened type)

The number next to the logo mark indicates items in stock for each brand.

TRUSCO

TRUSCO

Stock
38,650
Items

Long Eye Hook


RoHS

Com.eco
Chemical Content
Inspection

Com
Drawing



TLEH-4



- Features
- The opening widely opens, and the work of hanging things is efficient.
 - There is depth in the part to be hung, that can be hung with a thick tool.
- Use
- Set up on the wall, floor, pillar, etc., as a wall metal fitting for the chain, wire, and rope.
- Materials
- Stainless Steel (SUS304)
- Origin
- China

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	A (mm)	B (mm)	H (mm)	h (mm)	P (mm)	d (mm)	t (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
328-6053	TLEH-4	¥379	¥410	4	12	36	21.5	15	28	3.2	2.5	58.8/6	20	10
328-6061	TLEH-5	¥518	¥560	5	15	45	27.5	20	35	3.6	2.5	78.4/8	20	18
328-6070	TLEH-6	¥611	¥660	6	18	60	39.0	30	48	4.2	3.0	117.6/12	20	36
328-6088	TLEH-8	¥897	¥970	8	24	80	51.0	40	65	5.2	3.0	156.8/16	20	73

Contact us:0120-509-849 <http://www.orange-book.com/>

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

MIZUMOTO MACHINE

MM

Stock
529
Items


Long Eye Hook

RoHS

Com.eco
Chemical Content
Inspection



B-2193



- Features
- The opening widely opens, and the work of hanging things is efficient.
 - There is depth in the part to be hung, that can be hung with a thick tool.
- Use
- Set up on the wall, floor, pillar, etc., as a wall metal fitting for the chain, wire, and rope.
 - It is used for a hook of items on food processing sites.
- Materials
- Stainless Steel (SUS304)
- Origin
- China

Order Unit: 1 Piece

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	A (mm)	B1 (mm)	B2 (mm)	H (mm)	d (mm)	h (mm)	L (mm)	t (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
378-9616	B-2193	¥323	¥380	3	9	27	22	15	2.2	10	14	2	19.6/2	20	5
375-9857	B-2194	¥1,749	¥2,060	10	30	120	100	64	6.2	50	68	4	294.0/30	10	170

Contact us:079-246-2501 <http://www.mizumoto-mm.co.jp/>

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers

SUGATSUNE

SUGATSUNE

Stock
766
Items


Stainless Steel Hook

RoHS

Com
CAD



EP-25



- Features
- Since it is made of stainless steel, it is hard to rust.
- Use
- Working facilities, production facilities, machinery equipment, in an office, hospitals, etc.
- Materials
- Stainless steel (SCS13)
- Accessories
- Cross Recess Round Countersunk Wood Screw (stainless steel)
- Origin
- Japan

Order Unit: 1 Piece

(Price revision date: May, 2015) SUGATSUNE KOGYO Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	H (mm)	H1 (mm)	H2 (mm)	P (mm)	W (mm)	t (mm)	d (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
440-3711	EP-25	¥1,004	¥930	25	25	12	19	18	28	4	3	196/20	30	16
440-3720	EP-40	¥1,404	¥1,300	32	33	16	25	23	36	5	4	196/20	20	31

Contact us:03-3851-1122 <http://www.sugatsune.co.jp/>

TRUSCO

TRUSCO

Stock
38,650
Items


"Open Pad Eye"

RoHS

Com.eco
Chemical Content
Inspection



TOP-6



- Features
- Possible to install even on a narrow installation surface.
 - Please use the countersunk head screw.
- Use
- For attaching to a pole, a wall, etc.
- Materials
- Stainless Steel (SUS304)
- Origin
- China

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per bag)	D (mm)	A (mm)	B1 (mm)	H (mm)	P (mm)	d (mm)	t (mm)	Handing load (N/kgf)	Qty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
275-1992	TOP-5	¥917	¥990	5	15	45	20.0	35	4.2	2	98/10	2	20	28
275-2000	TOP-6	¥1,111	¥1,200	6	20	60	26.0	46	5.2	2	147/15	2	20	52
275-2018	TOP-8	¥897	¥970	8	26	80	32.5	60	5.2	3	196/20	1	20	63
275-2026	TOP-9	¥1,138	¥1,230	9	32	100	38.0	73	6.2	3	294/30	1	10	93

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

TRUSCO

Stock
38,650
Items

Wire Plate Hook

RoHS


Com.eco
Chemical Content
Inspection

Com
Drawing



TPH-5

TPH-6



- Features
- Since both sides of a round bar forming the hook part are welded, it can be used both for temporary hanging and tying.
- Use
- Setting on the wall, floor, pillar, etc., it is used as an edge bracket for the chain, wire, or rope.
 - It is used for temporary hanging a hose, etc.
- Materials
- Stainless Steel (SUS304)
- Origin
- China

Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	A (mm)	B (mm)	H (mm)	h (mm)	P (mm)	P1 (mm)	d (mm)	t (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
328-5961	TPH-4	¥703	¥760	4	40	12	31.5	16.5	32	-	3.2	2.0	68.6/7	20	18
328-5979	TPH-5	¥1,018	¥1,100	5	50	15	41.0	20.5	40	-	4.2	2.5	98.0/10	20	35
328-5987	TPH-6	¥1,537	¥1,660	6	54	30	48.0	23.0	42	18	5.2	2.5	147.0/15	20	66
328-5995	TPH-8	¥2,517	¥2,720	8	72	40	64.0	30.0	57	25	5.2	3.0	245.0/25	10	155

Contact us:0120-509-849 <http://www.orange-book.com/>