

The number next to the logo mark indicates items in stock for each brand.

TRUSCO Stock **38,650** Items

Flux



Features

- It is an aqueous solution type that does not solidify or absorb moisture.
- It can be used as it is, it is a resin bottle container easy to paint.

Use

- For brazing work.

Origin

- Japan

Order Unit: 1 Piece **TRZ-203** TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Comments	SPQ (piece)	Weight (g)
329-1529	TRZ-200	¥1,018	¥1,100	For silver solder	12	20
329-1537	TRZ-201	¥1,018	¥1,100	For aluminum hard brazing	12	20
329-1545	TRZ-203	¥1,018	¥1,100	For aluminum solder	12	20

Contact us: 0120-509-849 <http://www.orange-book.com/>

ASADA Stock **459** Items

"S Flux"



Features

- Japan Copper Development Association Guideline compliant product

Use

- Exclusive for soldering.
- For preventing oxidation and enhancing wetting when doing soldering work.

Origin

- Japan

Order Unit: 1 Piece **R50332N** ASADA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Comments	Activation temperature (°C)	Compatible base material	Capacity (ml)	Weight (g)
376-0430	R50332N	¥1,229	¥1,300	For soldering	180 to 400	Copper tube	100	130

Contact us: 052-911-7165 <http://www.asada.co.jp/>

Shin Fuji Stock **189** Items

Carbon Protector



Features

- Carbon fiber shuts out flame.

Materials

- Carbon fiber

Origin

- Japan

Order Unit: 1 Piece **RZ-401** SHINFUJI BURNER Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Dimension (mm)	Max Working Temperature (°C)	SPQ (piece)	Weight (g)
376-9330	RZ-401	¥1,157	¥1,500	250 x 180	500	5	35

Contact us: 0533-75-5000 <http://www.shin Fuji.co.jp/>

Shin Fuji Stock **189** Items

Ceramic Board



Features

- The honeycomb structure shuts out flame.

Materials

- Ceramic

Origin

- Japan

Order Unit: 1 Piece **RZ-400** SHINFUJI BURNER Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Dimension (mm)	Max Working Temperature (°C)	SPQ (piece)	Weight (g)
376-9321	RZ-400	¥1,157	¥1,500	93 x 66 x 13	1100	5	68

Contact us: 0533-75-5000 <http://www.shin Fuji.co.jp/>

ROTHENBERGER Stock **61** Items

Frame Guard "14-22"




Features

- Attach to a burner with a torch size from $\phi 14$ to 22mm to use.
- It shuts off flame and leads to improved heating efficiency (Heating speed increases by 30%).

Origin

- Germany



Order Unit: 1 Piece **R31043** ROTHENBERGER

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Applicable torch size (mm)	SPQ (piece)	Weight (g)
829-1517	R31043	¥5,481	¥5,800	$\phi 14$ to 22	1	100

Contact us: 052-911-7165 <http://www.asada.co.jp/>


ASADA Stock **459** Items

Carbon Electrode (2 pieces)



Origin

- Japan



Order Unit: 1 Set (Price revision date: Nov, 2015) ASADA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Model	Q'ty Per Set (piece)	Weight (g/set)
376-0057	44106	¥3,591	¥3,800	Electric brazing machine R-10, R-15, R-30	2	10

Contact us: 052-911-7165 <http://www.asada.co.jp/>

Shin Fuji Stock **189** Items

Support Stand



Features

- Essential item for brazing of small articles.
- Can be freely fixed 360 degrees.

Origin

- China

Order Unit: 1 Piece **RZ-300** SHINFUJI BURNER Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pole height (mm)	Clip width (mm)	SPQ (piece)	Weight (g)
376-9313	RZ-300	¥2,160	¥2,800	125	120	6	50

Contact us: 0533-75-5000 <http://www.shin Fuji.co.jp/>

Shin Fuji Stock **189** Items

Heat Resistant Gel



Features

- Insulates heat of a burner.
- Damage, overheating and distortion due to heat generated by welding or brazing can be prevented by applying it to the surface of base material.
- Incombustible, harmless, and non-corrosive.

Origin

- USA



Warning

- Freezing is strictly prohibited. Store it at 0 to 38°C.

Order Unit: 1 Piece **RZ403** SHINFUJI BURNER Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Content (g)	SPQ (piece)	Weight (kg)
432-0816	RZ403	¥1,929	¥2,500	Gel	400	24	0.5

Contact us: 0533-75-5000 <http://www.shin Fuji.co.jp/>