


Holders for Proximity Sensors / Sensor Flags / Sensor Flag Brackets


■ **Features:** Can be used in combination with Rails for Switches and Sensors - Aluminum (No. 4) on P.2077~P.2083

■ **Holders for Proximity Sensors**



RoHS 10

SBRK



Part Number		M	MxP (Fine)	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~50
SBRK	4	8	8x1.0		
		12	12x1.0		

♪ For orders larger than indicated quantity, please check with WOS.




Ordering Example **Part Number** - **M**
 SBRK4 - 8

■ **Sensor Flags**




RoHS 10


Round Pole
 DGSF
 KDGSF



Fully Threaded
 DGM
 KDGM



Fully Threaded Compact Flange
 DGMS
 KDGMS



Type	M	Material	S	Surface Treatment
Round Pole	DGSF	S45C	-	-
	KDGSF		-	Black Oxide
Fully Threaded	DGM		-	-
	KDGM		-	Black Oxide
Fully Threaded Compact Flange	DGMS		-	-
	KDGMS		-	Black Oxide

Part Number	Type	M (Coarse)	L	5mm Increment	D	W	DGSF Unit Price				KDGSF Unit Price							
							L50~100	L105~200	L205~400	L405~600	L50~100	L105~200	L205~400	L405~600				
Round Pole DGSF KDGSF		10		50~500	10	8												
		12			12	10												
		16		50~600	16	12												

Part Number	Type	M (Coarse)	L	5mm Increment	DGM Unit Price			KDGM Unit Price			
					L50~100	L105~200	L205~400	L50~100	L105~200	L205~400	
Fully Threaded DGM KDGM		10		50~400							
		12									
		16									

Part Number	Type	M (Coarse)	L	5mm Increment	S	W	DGMS Unit Price			KDGMS Unit Price			
							L50~100	L105~200	L205~400	L50~100	L105~200	L205~400	
Fully Threaded Compact Flange DGMS KDGMS		10		50~400	0≤S≤L-10	8							
		12				10							
		16				14							




Ordering Example **Part Number** - **L** - **S**
 DGSF10 - 150
 DGMS16 - 300 - 100

■ **Sensor Flag Brackets**



RoHS 10

DSB



Material: SS400
 Surface Treatment: Black Oxide

Part Number		Unit Price	Volume Discount Rate
Type	M (Coarse)	1 ~ 9 pc(s).	10~50
DSB	10		
	12		
	16		



Ordering Example **Part Number**
 DSB12

♪ For orders larger than indicated quantity, please check with WOS.



Example

