

Retaining Ring C Type (External) / Retaining Ring E Type (Boxes)




RoHS10

Retaining Rings - C Type (External)

Type	Material	Hardness
BOX-STWN	Spring Steel	44~53HRC
BOX-STWS	SUS304-CSP	36~44HRC

BOX-STWN
BOX-STWS (Stainless Steel)



No. 8 or Less

- Confirm detailed dimensions. P265
- Can be ordered as a single item. P265
- Installation Tools are available. P266



RoHS10

Retaining Rings - E Type

Type	Material	Hardness	Surface Treatment
BOX-NETW	Spring Steel	44~53HRC	Trivalent Chromate
BOX-NETWS	SUS304-CSP	37~46HRC	-

BOX-NETW
BOX-NETWS (Stainless Steel)



- Confirm detailed dimensions. P265
- Can be ordered as a single item. P265

When you order, please specify the box quantity.
Minimum order is 1 box.



Ordering Example

Part Number

BOX-STWN10
BOX-NETWS3

Box package is cost-saving for in-house stock or when large quantities are needed.

Part Number		Unit Price 1 ~ 10 Box(es)		Pcs./ Box
Type	No.	Price per PC.	1 Box	
BOX-STWN	3			2,000 pcs./box
	4			
	5			
	6			
	8			1,000 pcs./box
	10			
	12			
	15			
	20			500 pcs./box
	25			

For orders larger than indicated quantity, please check with WOS.

Part Number		Unit Price 1 ~ 10 Box(es)		Pcs./ Box	
Type	No.	Price per PC.	1 Box		
BOX-STWS (Stainless Steel)	4			2,000 pcs./box	
	5				
	6				
	8				
		10			1,000 pcs./box
		12			
		15			
		20			
	25			500 pcs./box	

For orders larger than indicated quantity, please check with WOS.

Part Number		Unit Price 1 ~ 10 Box(es)		Pcs./ Box	
Type	No.	Price per PC.	1 Box		
BOX-NETW	1.2			2,000 pcs./box	
	1.5				
	2				
	2.5				
	3				
	4				
		5			1,000 pcs./box
		6			
		7			
		8			

For orders larger than indicated quantity, please check with WOS.

Part Number		Unit Price 1 ~ 10 Box(es)		Pcs./ Box	
Type	No.	Price per PC.	1 Box		
BOX-NETWS (Stainless Steel)	1.2			2,000 pcs./box	
	1.5				
	2				
	2.5				
	3				
	4				
		5			1,000 pcs./box
		6			
		7			
		8			

For orders larger than indicated quantity, please check with WOS.