

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Balances

B Thermometers and Hygrometers

C Data-Loggers and Recorders

D Water and Soil Analysis

E Air and Gas Analysis

F Natural Environment Analysis

G Electrical Measuring Equipment

H Physical Property Measuring Equipment

I Microscopes

J Fiber Scopes and Loupes

K Lasers / Optical Equipment

L Measuring Tools

Thermo/Humidity Self Recorders

THERMO-HYGRO RECORDER

JP

Order No.	Model No.	Measuring Range (Temperature/Humidity)	JPY	Ref.No
1-8327-01	TH-27R	-20~+50°C/0~100% RH	¥ 47,000	045570
1-8327-12	C-20012-7	Recording Paper for 7days×55 sheets	¥ 2,500	045570
1-8327-13	C-20012-31	Recording Paper for 31days×15 sheets	¥ 2,500	045570
1-8327-19	PEN-R-ON2	Cartridge Pen Red×2pieces	¥ 3,000	045570
1-8327-20	PEN-BL-ON2	Cartridge Pen Blue×2pieces	¥ 3,000	045570
1-8327-21	PEN-BK-ON2	Cartridge Pen Black×2pieces	¥ 3,000	045570
1-8327-22	PEN-P-ON2	Cartridge Pen Purple×2pieces	¥ 3,000	045570

※ The recording paper is an option.

■ Feature

- Movement is also easy with a handle.
- The observation for one day or one year is possible by changing a dial switch.

■ Specification

- Min. Scale Value : Temperature/1°C, Humidity/1% RH
- Measuring System : Temperature/Bimetal, Humidity/Hair (Finishing Degreasing Processing)
- Power Supply : C Battery×2pieces (included for testing) ● Weight : 3kg
- Dimensions : 361×150×287mm ● Cartridge Pens (Purple) ×2pieces



Temperature and humidity

THERMO-HYGRO RECORDER

JP

Order No.	Model No.	Measuring Range (Temperature/Humidity)	JPY	Ref.No
1-1014-01	NS II-Q (quartz)	-15~+40°C/0~100% RH	¥ 54,500	045560
1-1014-02	NS II-S (manual winding)	100% RH	¥ 120,000	045560
1-1014-12	7210-60	Recording Paper for 1day (400sheets)	¥ 17,500	045560
1-1014-11	7210-62	Recording Paper for 7days (55sheets)	¥ 3,300	045560
1-1014-13	7210-64	Recording Paper for 32days (55sheets)	¥ 4,000	045560

※ Proofreading certificate issue is possible.

■ Feature

- Environmentally friendly and energy saving type as no power supply or battery is required (manual winding). ● Suitable for measuring in place where explosive and combustible materials are stored (manual winding).

■ Specification

- Min. Scale Value of Recording Paper : Temperature/1°C, Humidity/1% RH ● Accuracy : Temperature/ ±1°C (+10~30°C), ±2°C (other), Humidity/ ±3% RH (+20~95% RH), ±5% (other) ● Clock : NS II-Q/Switchable Among 1/7/32days, NS II-S/Switchable between 1/7days
- Measuring Method : Temperature/Bimetal, Humidity/Hair (specially processed) ● Dimensions : 336×148×295mm ● Weight : NS II-Q/3.1kg, NS II-S/3.3kg

■ Accessories

- Cartridge Pen (purple) ×2 (lasts approx.6months if used for 7days, however changes depending on usable conditions) ● Recording Paper for 7days×55sheets (year's supply) ×1book ● Binder for Recording Paper×1 ● C Battery×2 (only for NS II-Q)



Temperature and humidity

CARTRIDGE PEN

Order No.	Model No.	Specification	Quantity	JPY	Ref.No
1- 619-01	7238-04	Purple	1bag (1pen)	¥ 2,000	045560
1- 619-02	7238-08	Red		¥ 2,000	045560
1- 619-51	7238-02	Purple	1box (12pens)	¥ 19,800	045560
1- 619-52	7238-06	Red		¥ 19,800	045560

THERMO-HYGRO RECORDER(with test record)

JP

Order No.	Model No.	Measuring Range (temperature/humidity)	JPY	Ref.No
1-5065-01	NWR9903	-20~+50°C/0~100% RH	¥ 58,000	045550
1-5065-14	9900-54	Recording paper for 31 days(15 sheets)	¥ 1,200	045550
1-5065-11	9900-52	Recording paper for 7 days(55 sheets)	¥ 2,500	045550
N 1-5065-24	9900-N7	Cartridge pen - purple (1 pc)	¥ 1,800	045550
N 1-5065-25	9900-N8	Cartridge pen - red (1 pc)	¥ 1,800	045550
N 1-5065-22	9900-77	Cartridge pen - purple (1 pc)	¥ 1,800	045550
N 1-5065-23	9900-88	Cartridge pen - red (1 pc)	¥ 1,800	045550

※ When using devices with manufacturing numbers 7000 or lower, purchase cartridge pens 1-5065-22 (9900-77) · 1-5065-23 (9900-88) .

※ When using devices with manufacturing numbers 7001 or higher, purchase cartridge pens 1-5065-24 (9900-N7) · 1-5065-25 (9900-N8) .

■ Specification

- Min. graduation on recording paper : temperature/1°C, humidity/1%
- Measuring method : temperature/bimetal, humidity/hair (degreased)
- Measuring precision : temperature/±1.0°C, humidity/±3% (at 20°C)
- Clock : quartz clock · positive rotation drum ● Recording time : 1 day(24 h)~99 days (2376 h)
- Dimensions : 336×140×285mm ● Weight : 2.8kg
- Power supply : C battery×2 (included for testing)
- Recording paper for 7 days (55 sheets) included



Temperature and humidity