

スパーギヤ(ボス付) SUB

SUS
303



製品仕様

- 材質 SUS303(JIS G 4303)
- 歯形、精度 並歯、JISN8級(旧JIS4級)
- 圧力角 20°
- 表面処理 無し
- 歯面仕上 切削
- 穴径公差 JIS H7級

MP=1.0

製品記号	モジュール	歯数	ピッチ円直径	歯先円直径	歯幅	穴径	ボス径	ボス長	全長
	m		Z	P.C.D.		D	d	B	
SUB1016	1	16	16	18	12	8	18	13	25
SUB1017	1	17	17	19	12	8	19	13	25
SUB1018	1	18	18	20	10	8	15	10	20
SUB1019	1	19	19	21	10	8	16	10	20
SUB1020	1	20	20	22	10	8	16	10	20
SUB1021	1	21	21	23	10	8	18	10	20
SUB1022	1	22	22	24	10	8	18	10	20
SUB1023	1	23	23	25	10	8	20	10	20
SUB1024	1	24	24	26	10	8	20	10	20
SUB1025	1	25	25	27	10	8	20	10	20
SUB1026	1	26	26	28	10	8	22	10	20
SUB1027	1	27	27	29	10	8	22	10	20
SUB1028	1	28	28	30	10	10	24	10	20
SUB1029	1	29	29	31	10	10	24	10	20
SUB1030	1	30	30	32	10	10	25	10	20
SUB1032	1	32	32	34	10	10	25	10	20
SUB1034	1	34	34	36	10	10	26	10	20
SUB1035	1	35	35	37	10	10	26	10	20
SUB1036	1	36	36	38	10	10	28	10	20
SUB1038	1	38	38	40	10	10	28	10	20
SUB1040	1	40	40	42	10	10	30	10	20
SUB1042	1	42	42	44	10	10	30	10	20
SUB1044	1	44	44	46	10	10	30	10	20
SUB1045	1	45	45	47	10	10	30	10	20
SUB1046	1	46	46	48	10	10	30	10	20
SUB1048	1	48	48	50	10	10	30	10	20
SUB1050	1	50	50	52	10	10	35	10	20
SUB1052	1	52	52	54	10	10	35	10	20
SUB1054	1	54	54	56	10	10	35	10	20
SUB1055	1	55	55	57	10	10	35	10	20
SUB1058	1	58	58	60	10	10	35	10	20
SUB1060	1	60	60	62	10	10	35	10	20