

Ace フレキ

フレキシブル・チューブ (T型)



材質:SUS304

品番	寸法	定価	入数
PT-5015	1/2× 150 L	390	10
5020	200	430	10
5025	250	470	10
5030	300	500	10
5035	350	540	10
5040	400	570	10
5045	450	610	10
5050	500	650	10
5060	600	710	50
5070	700	780	50
5080	800	850	50
5090	900	950	50
5100	1000	1,020	50
PT-6015	3/4× 150 L	690	10
6020	200	740	10
6025	250	780	10
6030	300	830	10
6035	350	880	10
6040	400	1,010	10
6045	450	1,060	10
6050	500	1,100	10
6060	600	1,260	
6070	700	1,560	
6080	800	1,450	
6090	900	1,620	
6100	1000	1,760	

※ゴムパッキン2枚付

フレキチューブ用袋ナット

(BSBM製クロームメッキ仕上げ)




品番	寸法	定価
PH-NT04	PF1/2	130
NT06	PF3/4	230
NT08	PF 1	500

(SUS304製)

品番	寸法	定価
PH-7N04	PF1/2	740
7N06	3/4	1,080

フレキ用ニップル (Pニップル)

(BSBM製クロームメッキ仕上げ)



品番	寸法	定価
PN-1044	PF1/2 × PT1/2	180
1043	PT3/8	250
1066	PF3/4 × PT3/4	320
1064	PT1/2	380
1088	PF 1 × PT 1	950

(SUS304製)

品番	寸法	定価
PN-7044	PF1/2 × PT1/2	920
7066	3/4 × 3/4	1,180

フレキシブル・チューブ (H型)



材質:SUS316L

品番	寸法	定価	入数
PH-4015	1/2× 150 L	710	10
4020	200	760	10
4025	250	840	10
4030	300	960	10
4035	350	1,060	10
4040	400	1,130	10
4045	450	1,250	10
4050	500	1,370	10
4060	600	1,760	50
4070	700	2,150	50
4080	800	2,450	50
4090	900	2,780	50
4100	1000	3,200	50
PH-6015	3/4× 150 L	930	10
6020	200	1,020	10
6025	250	1,170	10
6030	300	1,260	10
6035	350	1,410	10
6040	400	1,500	10
6045	450	1,670	10
6050	500	1,830	10
6060	600	2,170	
6070	700	2,580	
6080	800	3,110	
6090	900	3,510	
6100	1000	4,260	
PH-8015	1 × 150 L	1,860	
8020	200	2,060	
8025	250	2,290	
8030	300	2,530	
8035	350	2,760	
8040	400	2,960	
8045	450	3,230	
8050	500	3,430	
8060	600	4,060	
8070	700	4,930	
8080	800	5,490	
8090	900	6,090	
8100	1000	6,660	

※V6500パッキン2枚付

フリーカット・チューブ

(SUS304製)

品番	寸法	定価
PT-5110	1/2 × 10m	7,700
6110	3/4 × 10m	13,400

フレキチューブ用パッキン



品番	寸法	定価
PH-AP04	1/2 (V-6500)	46
AP06	3/4 "	75
AP08	1 "	95
GP04	1/2 (ゴム)	20
GP06	3/4 "	35
GP08	1 "	85