

Standard cylinder

Accessories

Ordering code

F-JSI 50 CA

- Accessory
- Model
- Bore size
- Accessory type ①

FA: FA type
LB: LB type
CA: CA type
CB: CB type ②
CR: CR type
- Mounting accessory

① The listed accessories are for JSI cylinder. Accessories that are adaptable to other cylinders are not shown. Please refer to accessory list on P218 for selection and ordering information.

② CB is attached with relevant PIN.

Accessory selection

Accessories	JSI		JSID		JSIJ		
	Standard	With magnet	Standard	With magnet	Standard	With magnet	
Mounting accessory	LB	●	●	●	●	●	●
	FA	●	●	●	●	●	●
	FB	●	●	×	×	×	×
	CA	●	●	×	×	×	×
	CB	●	●	×	×	×	×
	CR	●	●	×	×	×	×
	TC	●	●	●	●	●	●
	TCM1	●	●	●	●	●	●
	TCM2	●	●	●	●	●	●
	Knuckle ①	I	●	●	●	●	●
Y		●	●	●	●	●	●
U		●	●	●	●	●	●
F		●	●	●	●	●	●
Sensor switch ②	CS1-B	×	●	×	●	×	●
	DS1-B	×	●	×	●	×	●
	CS1-F	×	●	×	●	×	●
	DS1-F	×	●	×	●	×	●
	CS1-U	×	●	×	●	×	●
DS1-U	×	●	×	●	×	●	

① Please refer to P453~456 for knuckle detail.

② Please refer to P457~480 for detail of sensor switch.


Material of accessories

Accessories	Mounting accessories										Knuckle			
	LB	FA	FB	CA	CB	CR	TC	TCM1	TCM2	I	Y	F	U	
Bore size 32-63	□	●	●	△	△	◇	◇	□	●	□	□	□	□	
80/100	□	●	●	△	△	◇	◇	□	●	□	□	□	□	
125	□	■	■	□	□	◇	◇	□	●	□	□	□	□	

●—Aluminum alloy, ■—Cast steel,
◇—Nodular cast iron, △—FC25; □—Carbon steel.



Dimensions

LB




Bore size/Item	AA	AC	AD	AE	AF	AG	AH	AP	AT
32	146	128	9	50	32	22	30	7	3
40	154	132	11	55	38	24	33	9	3
50	170	148	11	70	46	27	40	9	3
63	176	148	14	80	56	27	45	12	4
80	202	174	14	100	72	30	55	12	5
100	210	178	16	120	89	32	65	14	5
125	250	210	20	136	90	45	81	14	8

FA/FB



Bore size/Item	A	C	AJ	AK	BA	BB	BC	BD	BE	BF	BH	BP	T
32	131	84	11	6.5	30.5	10	47	32	80	64	6.5	7	32.5
40	135	84	11	6.5	35.5	10	53	36	90	72	6.5	9	38
50	152	94	14	9	40.5	12	65	45	108	90	8.5	9	46.5
63	152	94	14	9	45.5	12	75	50	118	100	8.5	9	56.5
80	186	114	17	11	45.5	16	95	63	150	126	10.5	12.5	72
100	186	114	17	11	55.5	16	115	75	176	150	10.5	14.5	89
125	217	120	19	13	60.5	20	138	102	216	180	12.5	14	110

CA



Bore size/Item	A	C	S	T	DC	DD	DE	DJ	DQ
32	131	84	46	32.5	23	10.5	10	13	13.8
40	135	84	52	38	23	11	10	13	13.8
50	152	94	65	46.5	30	15	14	17	19.8
63	152	94	75	56.5	30	15	14	17	19.8
80	186	114	95	72	42	23	22	27	29.8
100	186	114	114	89	42	23	22	27	29.8
125	217	120	136	110	50	28	25	28	31.8

