

50 mm Diameter Incremental Rotary Encoders

E50 Series



Features

- Ø 50 mm housing, Ø 8 mm solid shaft
- Accurate measurement of angle, position, revolution, speed, acceleration, and distance
- Cable type, cable connector type, axial / radial connector types available
- Various resolutions:
1 to 8000 pulses per revolution
- Various control output options
- Power supply:
5 VDC \pm 5%, 12 - 24 VDC \pm 5%

Specifications

Model	E50S8-□-□-T-□-□	E50S8-□-□-N-□-□	E50S8-□-□-V-□-□	E50S8-□-□-L-□-□
Resolution	1 / 2 / 5 PPR ⁰¹⁾ 10 to 8,000 PPR model			
Control output	Totem pole output	NPN open collector output	Voltage output	Line driver output
Output phase	A, B, Z	A, B, Z	A, B, Z	A, \bar{A} , B, \bar{B} , Z, \bar{Z}
Inflow current	≤ 30 mA	≤ 30 mA	-	≤ 20 mA
Residual voltage	≤ 0.4 VDC \pm	≤ 0.4 VDC \pm	≤ 0.4 VDC \pm	≤ 0.5 VDC \pm
Outflow current	≤ 10 mA	-	≤ 10 mA	≤ -20 mA
Output voltage (5 VDC \pm)	≥ (power supply -2.0) VDC \pm	-	-	≥ 2.5 VDC \pm
Output voltage (12 - 24 VDC \pm)	≥ (power supply -3.0) VDC \pm	-	-	≥ (power supply -3.0) VDC \pm
Response speed ⁰²⁾	≤ 1 μs			≤ 0.5 μs
Max. response freq.	300 kHz			
Max. allowable revolution ⁰³⁾	5,000 rpm			
Approval	CE EAC	CE EAC	CE EAC	CE EAC

01) Depending on the control output, only A, B or A, \bar{A} , B, \bar{B} are output.

02) Based on cable length: 2 m, 1 sink: 20 mA

03) Select resolution to satisfy Max. allowable revolution ≥ Max. response revolution

$$(\text{max. response revolution (rpm)}) = \frac{\text{max. response frequency}}{\text{resolution}} \times 60 \text{ sec}$$

Connection	Axial cable type	Axial cable connector type	Axial connector type	Radial connector type
Starting torque	≤ 0.007 N m		≤ 0.078 N m	
Inertia moment	≤ 80 g·cm ² (8 × 10 ⁻⁶ kg·m ²)		≤ 400 g·cm ² (4 × 10 ⁻⁵ kg·m ²)	
Allowable shaft load	Radial: ≤ 10 kgf, Thrust: ≤ 2.5 kgf			
Unit weight (packaged)	≈ 275 g (≈ 363 g)		≈ 180 g (≈ 268 g)	
Power supply	5 VDC \pm 5% (ripple P-P: ≤ 5%) / 12 - 24 VDC \pm 5% (ripple P-P: ≤ 5%) model			
Current consumption	Totem pole, NPN open collector, Voltage output: ≤ 80 mA (no load) Line driver output: ≤ 50 mA (no load)			
Insulation resistance	Between all terminals and case: ≥ 100 MΩ (500 VDC \pm megger)			
Dielectric strength	Between all terminals and case: 750 VAC ~ 50 / 60 Hz for 1 minute			
Vibration	1 mm double amplitude at frequency 10 to 55 Hz (for 1 minute) in each X, Y, Z direction for 2 hours			
Shock	≤ 75 G			
Ambient temp.	-10 to 70 °C, storage: -25 to 85 °C (no freezing or condensation)			
Ambient humi.	35 to 85%RH, storage: 35 to 90%RH (no freezing or condensation)			
Protection rating	Axial cable type / cable connector type: IP50 (IEC standard) ⁰¹⁾ Axial / Radial connector type: IP64 (IEC standard)			
Cable spec.	Ø 5 mm, 5-wire (Line driver output: 8-wire), shield cable cable type: 2 m, cable connector type: 250 mm			
Wire spec.	AWG24 (0.08 mm, 40-core), insulator diameter: Ø 1 mm			
Connector spec.	Totem pole, NPN open collector, Voltage output: M17 6-pin socket type Line driver output: M17 9-pin socket type			

01) Protection structure IP64 option is also available to order.

(starting torque: ≤ 0.078 N m, inertia moment: ≤ 400 g·cm² (4 × 10⁻⁵ kg·m²))



View product detail