





# HJ硬爪 北川油圧・エアチャック用



- 材質：SNCM21
- 硬度：HRC58~60



単位：mm

硬爪型式	希望小売価格 (1set3個入/円税別)	H-1	H-2	H-3	H-4	H-5	H-6	H-7	H-8	H-9	H-10	H-11	H-12	参考図
HJ05	31,000	53	23	28	10	4	30.5	14	22.5	10	M8	6	-	Fig.2
HJ06	32,000	67	31	36	12	5	39	20	28	12	M10	11	-	Fig.2
HJ08	38,500	86	35	51	14	5	31	25	18	12	M12	13.5	13.5	Fig.1
HJ10	48,500	100	40	54	16	5	43	30	17	14	M12	15	15	Fig.1
HJ12A-18	55,000	113	50	52	18	5	69.5	30	43.5	20	M14	32	-	Fig.2
HJ12A-21	71,000				21						M16			
HJ15-22	113,000	143	62	86	22	8	55	43	38	20	M20	40	40	Fig.1
HJ15-25.5	113,000				25.5									
HJ21	160,000	159	80	90	25	9	104	50	55	40	M20	55	55	Fig.3

## 北川硬爪兼用表

硬爪型式	共用チャック型式																		
	AS型	AT型 (2爪)	B-200型	B型 (B-A)	BB型 (BB-A)	BL型	BLT型 (2爪)	BS型	BT型 (2爪)	HO型	HOB型	HOBT型 (2爪)	HOH型	HOS型	N型	NL型	NLT型 (2爪)	NRC型	NT型 (2爪)
HJ05			204/205												04				
HJ06	06	06	206	06	206	206		306	06, 206	6		6	206		06	06	06	06	06
HJ08	08	08	208	08	208	208		308	08, 208	8		8	208		08	08	08	08	08
HJ10	10	10	210	10	210	210		310	10, 210	10		10	10K		10	10	10	10	10
HJ12A-18				12					12	12A		12	12K		12	12	12		12
HJ12A-21			212		212	212			212										
HJ15-22				15/18					15	15	15/18	15	15K	15					
HJ15-25.5			215												15/18				
HJ21				21/24											21/24				

**△注意** 硬爪の出荷単位：1セット3個入(チャックの爪数に応じた数量販売はしていません)