


MSM-Q

사각 연결 튜브

- 재료
산화피막 알루미늄 사각 튜브, 자연색, 무광택 마감 처리.
- 조립
 - MSM-Q-AL: 눈금 없음.
 - MSM-Q-AL-CS: 레이저로 새긴 정밀 눈금 (mm).




7

486

스페셜 요청
여러 가지 눈금.

플렉시블 자동화 부품



Elesa 표준				주요 치수				q
코드	설명	코드	설명	s	l	s1	l1	g
500451	MSM-Q-S10-100-AL	500453	MSM-Q-S10-100-AL-CS	10	100	7	15	11
500455	MSM-Q-S10-150-AL	500457	MSM-Q-S10-150-AL-CS	10	150	7	15	19
500459	MSM-Q-S10-200-AL	500461	MSM-Q-S10-200-AL-CS	10	200	7	15	25
500463	MSM-Q-S10-250-AL	500465	MSM-Q-S10-250-AL-CS	10	250	7	15	32
500467	MSM-Q-S10-300-AL	500469	MSM-Q-S10-300-AL-CS	10	300	7	15	38
500471	MSM-Q-S12-100-AL	500473	MSM-Q-S12-100-AL-CS	12	100	9	15	15
500475	MSM-Q-S12-150-AL	500477	MSM-Q-S12-150-AL-CS	12	150	9	15	23
500479	MSM-Q-S12-200-AL	500481	MSM-Q-S12-200-AL-CS	12	200	9	15	31
500483	MSM-Q-S12-250-AL	500485	MSM-Q-S12-250-AL-CS	12	250	9	15	39
500487	MSM-Q-S12-300-AL	500489	MSM-Q-S12-300-AL-CS	12	300	9	15	46
500491	MSM-Q-S16-100-AL	500493	MSM-Q-S16-100-AL-CS	16	100	13	20	21
500495	MSM-Q-S16-150-AL	500497	MSM-Q-S16-150-AL-CS	16	150	13	20	32
500499	MSM-Q-S16-200-AL	500501	MSM-Q-S16-200-AL-CS	16	200	13	20	43
500503	MSM-Q-S16-250-AL	500505	MSM-Q-S16-250-AL-CS	16	250	13	20	53
500507	MSM-Q-S16-300-AL	500509	MSM-Q-S16-300-AL-CS	16	300	13	20	64

