

OEM, OEMXT

LROEMXT

調整型・大型シリーズ

■ 油圧式（鉱物油）


■ 使用温度範囲：-10℃～+80℃

RoHS

※一部除く



寸法図



寸法図

型式	A (mm)	A1 (mm)	B (mm)	C (mm)	D (mm)	E (mm)	E1 (mm)	F (mm)	J (mm)	K (mm)	WF (mm)	WL (mm)	P (mm)	質量 (kg)
OEMXT1.5M x 1	144	162	58	M42 x 1.5	13	38	44	92	-	32	40.3	19.1	-	1.2
OEMXT1.5M x 2	195	213						118		45				1.7
OEMXT1.5M x 3	246	264						143		57				2.1
OEMXT2.0M x 2	226	243	77	M64 x 2.0	19	50	57	140	-	51	61.5	-	-	3.6
OEMXT2.0M x 4	328	345						191		76				4.9
OEMXT2.0M x 6	456	473						241		76				6.4
OEM3.0M x 2	245	265	98	M85 x 2.0	22	69	76	140	58	51	-	-	-	7.0
OEM3.0M x 3.5	323	343						180		71				9.1
OEM3.0M x 5	399	419						217		71				10.9
OEM3.0M x 6.5	494	514				81	81	256						13.6
OEM4.0M x 2	313	335	127	M115 x 2.0	35	88	95	203	74.0	80	-	-	38	15.0
OEM4.0M x 4	414	436						254		105				18.2
OEM4.0M x 6	516	539						308		108				20.0
OEM4.0M x 8	643	666						354		108				30.0
OEM4.0M x 10	745	767						407						33.0
LROEMXT1.5M x 1	144	162	58	M42 x 1.5	13	38	44	92	-	32	40.3	19.1	-	1.2
LROEMXT1.5M x 2	195	213						118		45				1.7
LROEMXT2.0M x 2	226	243						140		51				2.1

※ OEM3.0M, OEM4.0M シリーズは非 RoHS です。

※ A1 と φ E1 はオプションのウレタンキャップを取付けた時の寸法です。