



FITTING

U

EQUAL UNION

フレアードユニオン



(METRIC)

(Unit:mm)

| TUBE O.D. T | PART. No. | A | C | D | E | F | G | H |
|----------------|-----------|------|------|------|-----|----|-------|----|
| 2 | U- 2-0 | 26 | 9.5 | 1.3 | 8 | 8 | 17.5 | |
| 3 | U- 3-0 | 38 | 16 | 15 | 2.5 | 12 | 14 | 24 |
| 4 | U- 4-0 | 43.6 | 18.3 | 15.3 | 3.5 | 14 | 14 | 29 |
| 6 | U- 6-0 | 43.8 | 18.4 | 15.4 | 5 | 14 | 14 | 29 |
| 8 | U- 8-0 | 44.6 | 18.8 | 16.8 | 6 | 14 | 15.87 | 29 |
| 10 | U-10-0 | 48.4 | 20.7 | 18.7 | 8 | 17 | 19 | 31 |
| 12 | U-12-0 | 52.6 | 22.8 | 22.8 | 10 | 22 | 23 | 31 |
| 14 | U-14-0 | 54 | 23.5 | 24.5 | 12 | 23 | 26 | 33 |
| 15 | U-15-0 | 53 | 23 | 24 | 12 | 23 | 26 | 33 |
| 16 | U-16-0 | 54 | 23.5 | 24.5 | 12 | 23 | 26 | 33 |
| 18 | U-18-0 | 58 | 24 | 25 | 15 | 27 | 30 | 36 |
| 20 | U-20-0 | 58 | 24 | 25 | 17 | 30 | 32 | 36 |
| 22 | U-22-0 | 60.4 | 25.2 | 25.2 | 18 | 30 | 35 | 38 |
| 25 | U-25-0 | 69 | 28.5 | 33.5 | 22 | 35 | 38 | 40 |

(INCHES)

※管外径5φも製作しております。

| | | | | | | | | |
|-------------|---------|------|------|------|-----|----|-------|------|
| 1/16": 1.6 | U-005-0 | 25 | 11.4 | 9 | 1.3 | 8 | 8 | 17.5 |
| 1/8": 3.18 | U- 01-0 | 38 | 16 | 15 | 2.5 | 12 | 14 | 24 |
| 1/4": 6.35 | U- 02-0 | 43.8 | 18.4 | 15.4 | 5 | 14 | 14 | 29 |
| 5/16": 7.94 | U-025-0 | 44.6 | 18.8 | 16.8 | 6 | 14 | 15.87 | 29 |
| 3/8": 9.53 | U- 03-0 | 47.6 | 20.3 | 17.8 | 7 | 17 | 17.46 | 31 |
| 1/2": 12.7 | U- 04-0 | 52.6 | 22.8 | 22.8 | 10 | 22 | 23 | 31 |
| 5/8": 15.87 | U- 05-0 | 53 | 23 | 24 | 12 | 23 | 26 | 33 |
| 3/4": 19.05 | U- 06-0 | 58 | 24 | 25 | 16 | 27 | 26 | 36 |
| 7/8": 22.23 | U- 07-0 | 60.4 | 25.2 | 25.2 | 18 | 30 | 35 | 38 |
| 1": 25.4 | U- 08-0 | 68 | 28 | 33 | 22 | 35 | 38 | 40 |

(SCHEDULE)

※管外径3/8φも製作しております。



| | | | | | | | | |
|--------------|----------|------|------|------|----|----|----|----|
| 1/8" B: 10.5 | U-10.5-0 | 49.4 | 21.2 | 19.2 | 8 | 17 | 19 | 31 |
| 1/4" B: 13.8 | U-13.8-0 | 53 | 23 | 24 | 12 | 23 | 26 | 33 |
| 3/8" B: 17.3 | U-17.3-0 | 58 | 24 | 25 | 15 | 27 | 30 | 36 |
| 1/2" B: 21.7 | U-21.7-0 | 60.4 | 26.5 | 25.2 | 18 | 30 | 35 | 38 |

A.C.D:FINGER TIGHT-±0.5mm (about)

BU

BULKHEAD UNION

隔壁フレアードユニオン



(METRIC)

(Unit:mm)

| TUBE O.D. T | PART. No. | A | B | C | D | E | F | G | H | Panel Hole Size | Max. Panel Thickness |
|----------------|-----------|------|----|------|------|-----|----|-------|------|-----------------------|----------------------------|
| 3 | BU- 3-0 | 50 | 22 | 16 | 15 | 2.5 | 14 | 12 | 36 | 8.5 | 10 |
| 4 | BU- 4-0 | 60.1 | 28 | 18.3 | 15.3 | 3.5 | 17 | 14 | 45.5 | 11.5 | 13 |
| 6 | BU- 6-0 | 60.3 | 28 | 18.4 | 15.4 | 5 | 17 | 14 | 45.5 | 11.5 | 13 |
| 8 | BU- 8-0 | 62.6 | 29 | 18.8 | 16.8 | 6 | 17 | 15.87 | 47 | 13.2 | 13.5 |
| 10 | BU-10-0 | 66.4 | 30 | 20.7 | 18.7 | 8 | 22 | 19 | 49 | 16.2 | 14.5 |
| 12 | BU-12-0 | 73.6 | 32 | 22.8 | 22.8 | 10 | 26 | 23 | 52 | 19.5 | 16 |
| 14 | BU-14-0 | 76 | 34 | 23.5 | 24.5 | 12 | 27 | 26 | 55 | 22.8 | 17 |
| 15 | BU-15-0 | 75 | 34 | 23 | 24 | 12 | 27 | 26 | 55 | 22.8 | 17 |
| 16 | BU-16-0 | 76 | 34 | 23.5 | 24.5 | 12 | 27 | 26 | 55 | 22.8 | 17 |
| 18 | BU-18-0 | 81 | 34 | 24 | 25 | 15 | 32 | 30 | 59 | 26 | 17 |
| 20 | BU-20-0 | 81 | 36 | 24 | 25 | 17 | 32 | 32 | 59 | 27.5 | 17 |
| 22 | BU-22-0 | 82.4 | 46 | 25.2 | 25.2 | 18 | 35 | 35 | 60 | 29.2 | 17 |
| 25 | BU-25-0 | 99 | 44 | 29.3 | 33.5 | 22 | 42 | 38 | 70 | 33.3 | 24 |

(INCHES)

※管外径5φも製作しております。

| | | | | | | | | | | | |
|-------------|----------|------|----|------|------|-----|----|-------|------|------|------|
| 1/8": 3.18 | BU- 01-0 | 50 | 22 | 16 | 15 | 2.5 | 14 | 12 | 36 | 8.5 | 10 |
| 1/4": 6.35 | BU- 02-1 | 60.3 | 28 | 18.4 | 15.4 | 5 | 17 | 14 | 45.5 | 11.5 | 13 |
| 5/16": 7.94 | BU-025-0 | 62.6 | 29 | 18.8 | 16.8 | 6 | 17 | 15.87 | 47 | 13.2 | 13.5 |
| 3/8": 9.53 | BU- 03-0 | 65.6 | 30 | 20.3 | 17.8 | 7 | 19 | 17.46 | 49 | 14.8 | 14.5 |
| 1/2": 12.7 | BU- 04-0 | 73.6 | 32 | 22.8 | 22.8 | 10 | 26 | 23 | 52 | 19.5 | 16 |
| 5/8": 15.87 | BU- 05-0 | 75 | 34 | 23 | 24 | 12 | 27 | 26 | 55 | 22.8 | 17 |
| 3/4": 19.05 | BU- 06-0 | 81 | 34 | 24 | 25 | 15 | 32 | 30 | 59 | 26 | 17 |
| 7/8": 22.23 | BU- 07-0 | 82.4 | 36 | 25.2 | 25.2 | 18 | 35 | 35 | 60 | 29.2 | 17 |
| 1": 25.4 | BU- 08-0 | 98 | 44 | 28 | 33 | 22 | 42 | 38 | 70 | 33.3 | 24 |

(SCHEDULE)

※管外径3/8φも製作しております。

| | | | | | | | | | | | |
|--------------|-----------|------|----|------|------|----|----|----|----|------|------|
| 1/8" B: 10.5 | BU-10.5-0 | 67.4 | 30 | 21.2 | 19.2 | 8 | 22 | 19 | 49 | 16.2 | 14.5 |
| 1/4" B: 13.8 | BU-13.8-0 | 75 | 34 | 23 | 24 | 12 | 27 | 26 | 55 | 22.8 | 17 |
| 3/8" B: 17.3 | BU-17.3-0 | 81 | 34 | 24 | 25 | 15 | 32 | 30 | 59 | 26 | 17 |
| 1/2" B: 21.7 | BU-21.7-0 | 82.4 | 36 | 25.2 | 31.5 | 18 | 35 | 35 | 60 | 29.2 | 17 |

A.C.D:FINGER TIGHT-±0.5mm (about)