

샤프트 / C-와셔 • DIN 6340 열처리
EH 23060.




제품 설명

재질

- 열처리 스틸, 열처리, 펀치 타발, 인산염 처리

그림



주문 정보

d ₁	치수 d ₂ [mm]	s	스크류용 [mm]	📦 [g]	부품번호.
6,4	17	3	M 6	3,8	23060.0006
8,4	23	4	M 8	9,8	23060.0008
10,5	28	4	M10	14,0	23060.0010
13,0	35	5	M12	28,0	23060.0012
15,0	40	5	M14	40,0	23060.0014 ¹⁾
17,0	45	6	M16	55,0	23060.0016
19,0	45	6	M18	53,0	23060.0018 ¹⁾
21,0	50	6	M20	71,0	23060.0020
23,0	50	8	M22	86,0	23060.0022 ¹⁾
25,0	60	8	M24	122,0	23060.0024
31,0	68	10	M30	214,0	23060.0030
38,0	80	12	M36	360,0	23060.0036 ¹⁾

¹⁾ 이 치수들은 DIN 규격이 아님.

적용 예

