

클램프 • DIN 6314 평평한 면
EH 23140.




제품 설명

재질

- 열처리 스틸, 에나멜 코팅

그림



주문 정보

기본 치수 b_1 [mm]	l	a	치수 [mm]				스크류용		[g]	부품번호.
			b_2	b_3	e_1	e_2	[mm]	[인치(inch)]		
6,6	50	10	20	8	10	20	M 6	1/4	61	23140.0007
9,0	60	12	25	10	13	22	M 8	5/16	112	23140.0009
11,0	80	15	30	12	15	30	M10	3/8	228	23140.0011
14,0	100	20	40	14	21	40	M12, M14	1/2	492	23140.0014
	125	20	40	14	21	50	M12, M14	1/2	623	23140.0015
18,0	125	25	50	18	26	45	M16, M18	5/8	980	23140.0018
	160	25	50	18	26	65	M16, M18	5/8	1246	23140.0019
22,0	160	30	60	22	30	60	M20, M22	3/4	1793	23140.0022
	200	30	60	22	30	80	M20, M22	3/4	2244	23140.0023
26,0	200	30	70	26	35	80	M24	1	2617	23140.0026
	250	30	70	26	35	105	M24	1	3823	23140.0027
33,0	250	40	80	34	45	100	M30	1 1/4	4980	23140.0034
	315	50	80	34	45	130	M30	1 1/4	7840	23140.0035

적용 예

