



PC/PF/PFR/PFA series

조절자

kg 200 ~ 1,000 kg

✓ RoHS



재질		
볼트/너트	PC	카본 스틸
	PF	
	PFR	
	PFA	
패드	PC	프레스 스틸+TPR
	PF	프레스 스틸
	PFR	프레스 스틸+NBR
	PFA	프레스 스틸
표면처리	전체	니켈도금 / 광택처리

모델	L1	L	H1	H	B	A	Kg/4개
PC-8	40	57.5	11	6.5	Ø36	M8x1.25	200
	80	97.5					
PC-10	60	81	13	8	Ø48	M10x1.5	300
	100	121					
PC-12	60	82	13	9	Ø48	M12x1.75	500
	90	112					
	120	142					
	150	172					
PC-16	50	76	15	11	Ø58	M16x2.0	800
	80	106					
	100	126					
	130	156					
	150	176					
	180	206					
PC-20	100	129	14	14	M20x2.5	1,000	
	130	159					
	150	179					
	180	209					
200	229						

Unit : mm

모델	L1	L	H1	H	B	A	Kg/4개
PF-8	40	57	10.5	6.5	Ø37	M8x1.25	200
	80	97					
PF-10	60	81	13.5	8	Ø54	M10x1.5	300
	100	121					
PF-12	60	82	13.5	9	Ø54	M12x1.75	500
	90	112					
	120	142					
	150	172					
PF-16 SPF-16 (Stainless Steel)	50	79	17	11	Ø74	M16x2.0	800
	80	109					
	100	129					
	130	159					
	150	179					
	180	209					
PF-20 SPF-20 (Stainless Steel)	100	131	14	14	M20x2.5	1,000	
	130	161					
	150	181					
	180	211					
200	231						

모델	L1	L	H1	H	B	A	Kg/4개
PFR-8	40	61	15	6.5	Ø43	M8x1.25	200
	80	101					
PFR-10	60	86	18	8	Ø60	M10x1.5	300
	100	126					
PFR-12	60	87	18	9	Ø60	M12x1.75	500
	90	117					
	120	147					
	150	177					
PFR-16 SPFR-16 (Stainless Steel)	50	84	22.5	11	Ø80	M16x2.0	800
	80	114					
	100	134					
	130	164					
	150	184					
	180	214					
PFR-20 SPFR-20 (Stainless Steel)	100	136	14	14	M20x2.5	1,000	
	130	166					
	150	186					
	180	216					
200	236						

모델	L1	L	H1	H	B	A	Kg/4개
PFA-10	60	85	17	8	Ø74	M10x1.5	300
	100	125					
PFA-12	60	86	17	9	Ø74	M12x1.75	500
	90	116					
	120	146					
	150	176					
PFA-16 SPFA-16 (Stainless Steel)	50	79	17	11	Ø74	M16x2.0	800
	80	109					
	100	129					
	130	159					
	150	179					
	180	209					
PFA-20 SPFA-20 (Stainless Steel)	100	131	14	14	M20x2.5	1,000	
	130	161					
	150	181					
	180	211					
200	231						