

固定減衰器 (SMAタイプ) (DC~18.0GHz)

■仕様

製品番号 Part No.	減衰量 (dB) Attenuation		V.S.W.R. (Max)			電力 (W) Power	コネクタ Connectors	質量 (g) Weight
	DC~12.4GHz	12.4~18GHz	DC~4GHz	4~12.4GHz	12.4~18GHz			
AT-100-(0) (40)	0 ^{+0.5} ₀	0 ^{+1.0} ₀	1.15	1.20	1.30	1	HRM-J・P	8
AT-100-(0.5) (40)	0.5±0.5	0.5 ^{+1.0} _{-0.5}	1.15	1.20	1.30	1	HRM-J・P	8
AT-101 (40)	1±0.5	1±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-100-(1.5) (40)	1.5±0.5	1.5±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-102 (40)	2±0.5	2±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-100-(2.5) (40)	2.5±0.5	2.5±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-103 (40)	3±0.5	3±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-100-(3.5) (40)	3.5±0.5	3.5±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-104 (40)	4±0.5	4±1.0	1.15	1.20	1.30	1	HRM-J・P	8
AT-105 (40)	5±0.7	5±1.2	1.15	1.20	1.30	1	HRM-J・P	8
AT-106 (40)	6±0.7	6±1.2	1.15	1.20	1.30	1	HRM-J・P	8
AT-107 (40)	7±0.7	7±1.2	1.15	1.20	1.30	1	HRM-J・P	8
AT-108 (40)	8±0.7	8±1.2	1.15	1.20	1.30	1	HRM-J・P	8
AT-109 (40)	9±1.0	9±1.25	1.15	1.20	1.30	1	HRM-J・P	8
AT-110 (40)	10±1.0	10±1.25	1.15	1.20	1.30	1	HRM-J・P	8
AT-112 (40)	12±1.0	12±1.25	1.15	1.20	1.30	1	HRM-J・P	8
AT-113 (40)	13±1.0	13±1.25	1.15	1.20	1.30	1	HRM-J・P	8
AT-114 (40)	14±1.2	14±1.3	1.15	1.20	1.30	1	HRM-J・P	8
AT-115 (40)	15±1.2	15±1.3	1.15	1.20	1.30	1	HRM-J・P	8
AT-120 (40)	20±1.2	20±1.3	1.15	1.20	1.30	1	HRM-J・P	8
AT-203 (40)	3±0.5	3±1.0	1.15	1.20	1.30	1	HRM-P・P	9
AT-206 (40)	6±0.7	6±1.2	1.15	1.20	1.30	1	HRM-P・P	9
AT-210 (40)	10±1.0	10±1.25	1.15	1.20	1.30	1	HRM-P・P	9
AT-220 (40)	20±1.2	20±1.3	1.15	1.20	1.30	1	HRM-P・P	9
AT-303 (40)	3±0.5	3±1.0	1.15	1.20	1.30	1	HRM-J・J	7
AT-306 (40)	6±0.7	6±1.2	1.15	1.20	1.30	1	HRM-J・J	7
AT-310 (40)	10±1.0	10±1.25	1.15	1.20	1.30	1	HRM-J・J	7
AT-320 (40)	20±1.2	20±1.3	1.15	1.20	1.30	1	HRM-J・J	7

製品番号 Part No.	減衰量 (dB) Attenuation		V.S.W.R. (Max)		電力 (W) Power	コネクタ Connectors	質量 (g) Weight
	DC~8GHz		DC~4GHz	4~8GHz			
AT-126 (40)	26±1.0		1.15	1.20	1	HRM-J・P	8
AT-130 (40)	30±1.2		1.15	1.20	1	HRM-J・P	8