


Industrial Hose


For Machine Tools, Plastic Molding Machine, or Facilities



E-KYS KY SUNFOODS HOSE

E-KYS · E-KYS does not produce harmful gas very much even if it is burned out. Thus it is very environmentally-friendly hose.
 · The inner layer is good at chemical resistance due to the usage of olefin resin. (For more information on chemical resistance data, please refer to page 16.)

EIGHTRON®




| Model Number | I.D. × O.D. mm | Working Pressure (MPa) | | Minimum Bend Radius (20°C) mm | Temperature Range °C | Standard Length m | Weight g/m | Package Type | Color |
|--------------|-------------------|------------------------|---------|----------------------------------|-------------------------|----------------------|---------------|---------------|---------|
| | | at 20°C | at 65°C | | | | | | |
| E-KYS-6 | 6 × 11 | | | 45 | | 100 | 65 | | |
| E-KYS-8 | 8 × 13.5 | | | 60 | | 100 | 90 | | |
| E-KYS-9 | 9 × 15 | | | 65 | | 100 | 110 | | |
| E-KYS-10 | 10 × 16 | 0 ~ 0.8 | 0 ~ 0.4 | 70 | | 100 | 120 | | |
| E-KYS-12 | 12 × 18 | | | 85 | | 100 | 140 | | |
| E-KYS-15 | 15 × 22 | | | 105 | 0 ~ 65 | 50 | 205 | Film Wrapping | Natural |
| E-KYS-19 | 19 × 26 | | | 135 | | 50 | 245 | | |
| E-KYS-25 | 25 × 33 | 0 ~ 0.5 | 0 ~ 0.3 | 175 | | 50 | 360 | | |
| E-KYS-32 | 32 × 41 | 0 ~ 0.4 | 0 ~ 0.2 | 225 | | 50 | 510 | | |
| E-KYS-38 | 38 × 48 | | | 265 | | 50 | 640 | | |
| E-KYS-50 | 50 × 62 | 0 ~ 0.3 | 0 ~ 0.2 | 400 | | 50 | 1,000 | | |


*When installing EIGHTLOCK®, values shown above are not guaranteed. For more information, please refer to page 28.

DATA Relationship between Working Temperature and Maximum Working Pressure


E-TB: PRESSURE HOSE



E-SP: Spring Hose



E-STB: Oil-Proof PRESSURE HOSE



E-KYS: KY SUNFOODS HOSE

