

K-140 / 141 / 142 POLISHING PADS




- The fine-grade abrasive prevents clogging and facilitates smooth working.
- Removes surface rust and soiling without damaging the base material.
- Cleans the soldering iron tip better than paste types.
- Heat resistant temp.: 60 to 70°C



Part no.	Abrasive grain	Application example	Material	Size mm	Color
K-140	#60	Metal sheet rust removal	NBR foam with abrasive	50 × 25.5 × 20	Black
K-141	#120	Aluminum sheet deburring			
K-142	#320	Soldering iron tip oxide removal			



Metal surface rust removal



Aluminum sheet deburring



Soldering iron tip cleaning
(The soldering iron tip should be cooled before cleaning it.)

An instruction video is available on our website for your reference.
<http://www.hozan.co.jp/animation/>

K-35 DEBURRING TOOL

- 3 blade types are provided. One for steel, copper, and aluminum, one for plastic, and one for general-purpose.
- Blade length: 10 mm
- Weight: 35 g




For deburring metal pipe



Work is also possible from the burred reverse side




For drilled hole deburring



For cut face deburring



The blade can be stowed inside the body.



An instruction video is available on our website for your reference.
<http://www.hozan.co.jp/animation/>

Replacement parts K-35-1 / 2 / 3 REPLACEMENT BLADES


- Quantity: 2 pieces
- Application: K-35-1 for steel (black, flat leaf)
- K-35-2 for plastic (silver, double blade)
- K-35-3 all-purpose (black, double blade)




K-35-2

K-203 PIPE CUTTER

- Pipe types: Stainless and copper pipes.
- Pipe sizes: 3 to 32 mmφ (1/8" to 1 1/4"φ)
- OAL: 130mm
- Weight: 205 g
- Accessories: Replacement blade (K-203-1).




To cut, turn in the arrow direction.



To repair a new flare, place the flare in the roller groove and cut at its base. This minimizes pipe loss.



With blade for chamfering



The replacement blade is located as shown in the illustration.

Replacement parts K-203-1 / 11 REPLACEMENT BLADES

- Application: K-203-1 for stainless & copper pipe
- Dedicated K-203-11 for copper pipe.
- * Dedicated item is recommended for copper pipe cutting.
- The thin blade minimizes outer dia. changes and burrs on the finished product.



K-203-1

K-129S HACKSAW

- Saw blade: 250 mm
- OAL: 450mm
- Weight: 430 g
- Accessories: 12 replacement blades (K-126).



Replacement part K-126 REPLACEMENT BLADE

- OAL: 250mm
- Teeth pitch: 32 / inch
- Quantity: 12 pieces



Warning ● Always wear safety glasses when using this product.

Technical inquiries can be made by E-mail to the following address: th@hozan.co.jp

Cutters & Pliers

Wire strippers

Crimpers

Tweezers

Screwdrivers & Wrenches

Metal working

Parts boxes

Tool cases

Tool kits

Soldering irons & Solder

Parts & Solder removal equipment

Measuring instruments

Optical equipment

Antistatic products

Clean products

Chemical products

Maintenance & Safety products

Milling machine

Pattern cutters

Desk drill presses

Circular saws

PCB cutter

Band saw

Sheet metal bender

Drilling tools

Polishing pads

Pipe cutter

Files

Sand blaster