





カットグリップ内径加工用チップ



GEPI...RX/LX (外周研削タイプ隅加工チップ) 販売単位：10個

型番	寸法 (mm)				PVDコーティング	
	W±0.02	R±0.03	M	Tmax	IC528	
GEPI 1.00-0.1RX	1.00	0.1	1.8	1.5	●	
GEPI 1.00-0.1LX	1.00	0.1	1.8	1.5	●	



適合ホルダー：GEHIR/L・GEHIMR/L D66頁
アダプター：GEAIR/L D67頁



GEPI...UR/UL/UN (外周研削タイプ盗み加工チップ) 販売単位：10個

型番	寸法 (mm)				PVDコーティング		超微粒子超硬
	W±0.02	R±0.05	M	Tmax	IC528	IC08	
GEPI 2.00-1.00UR	2.00	1.0	1.8	2.0	●	○	
GEPI 2.00-1.00UL	2.00	1.0	1.8	2.0	●	○	
GEPI 3.00-1.50UN	3.00	1.5	2.2	2.0	●		

適合ホルダー：GEHIUR/L D71頁



GEPI...MT/WT (外周研削タイプねじ切チップ) 販売単位：10個

型番	α°	寸法 (mm)				PVDコーティング		超微粒子超硬
		ピッチmin	W±0.02	R±0.03	M	IC908	IC08	
GEPI 2.5-MT0.05	60°	0.90	2.50	0.05	1.8	●	○	
GEPI 2.5-WT0.05	55°	0.47	2.50	0.05	1.8	●	○	

最大ピッチは2.5mm以下

適合ホルダー：GEHIR/L D66頁
GEHIMR/L D66頁
GEHSR/L-SL B14頁
アダプター：GEAIR/L D67頁