




仕上刃(さらえ刃)無タイプ55°ねじ切りチップ
仕上刃(さらえ刃)無タイプ60°ねじ切りチップ



I/ERMタイプ

Uタイプ

外径ねじ用 (55°)

販売単位: 5個

形状	型番	用途		寸法(mm)					PVDコーティング					超微粒子超硬
		ピッチ	山数	d	l	r	x	y	IC228	IC808	IC908	IC1007	IC08	
	11ER A 55	0.50-1.50	48-16	6.350	11	0.05	0.8	0.9			○			
	16ER A 55	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9			●			
	16ER G 55	1.75-3.00	14-8	9.525	16	0.20	1.2	1.7			●			
	16ER AG 55	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●			
	16ERB G 55	1.75-3.00	14-8	9.525	16	0.20	1.2	1.7			●			
	16ERB AG 55	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●			
	16ERM G 55	1.75-3.00	14-8	9.525	16	0.23	1.2	1.7		▲	●			
	16ERM AG 55	0.50-3.00	48-8	9.525	16	0.07	1.2	1.7		▲	●	▲		

内径ねじ用 (55°)

販売単位: 5個

形状	型番	用途		寸法(mm)					PVDコーティング					超微粒子超硬
		ピッチ	山数	d	l	r	x	y	IC228	IC808	IC908	IC1007	IC08	
	06IR A 55	0.50-1.25	48-20	3.969	6	0.05	0.6	0.6	●					
	08IR A 55	0.50-1.50	48-16	4.763	8	0.05	0.6	0.7	●					
	11IR A 55	0.50-1.50	48-16	6.350	11	0.05	0.8	0.9			●			
	16IR AG 55	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●			
	22IR N 55	3.50-5.00	7-5	12.700	22	0.42	1.7	2.5			●			
	08UIRL U 55	1.75-2.00	14-11	4.763	8	0.10	0.8	4.0	●					
	16IRB G 55	1.75-3.00	14-8	9.525	16	0.20	1.2	1.7			●			
	16IRB AG 55	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			○			
	16IRM G 55	1.75-3.00	14-8	9.525	16	0.20	1.2	1.7		▲	●			
	16IRM AG 55	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7		▲	●			

外径ねじ用 (60°)

販売単位: 5個

形状	型番	用途		寸法(mm)					PVDコーティング					超微粒子超硬
		ピッチ	山数	d	l	r	x	y	IC228	IC808	IC908	IC1007	IC08	
	11ER A 60	0.50-1.50	48-16	6.350	11	0.05	0.8	0.9			●			
	16ER A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9			●			
	16ER G 60	1.75-3.00	14-8	9.525	16	0.17	1.2	1.7			●			
	16ER AG 60	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●	▲		
	22ER N 60	3.50-5.00	7-5	12.700	22	0.32	1.7	2.5			●			
	27ER Q 60	5.50-6.00	4.5-4	15.880	27	0.63	2.1	3.1			●			
	16ERB A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9			●			
	16ERB G 60	1.75-3.00	14-8	9.525	16	0.17	1.2	1.7			●			
	16ERB AG 60	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●			
	16ERM A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9		▲	●	▲		
	16ERM G 60	1.75-3.00	14-8	9.525	16	0.17	1.2	1.7		▲	●	▲		
	16ERM AG 60	0.50-3.00	48-8	9.525	16	0.06	1.2	1.7		●	●	▲		
	22ERM N 60	3.50-5.00	7-5	12.700	22	0.32	1.7	2.5		▲	●	▲		

内径ねじ用 (60°)

販売単位: 5個

形状	型番	用途		寸法(mm)					PVDコーティング					超微粒子超硬
		ピッチ	山数	d	l	r	x	y	IC228	IC808	IC908	IC1007	IC08	
	06IR A 60	0.50-1.25	48-20	3.969	6	0.05	0.5	0.6	●					
	08IR A 60	0.50-1.50	48-16	4.763	8	0.05	0.6	0.7	●					
	11IR A 60	0.50-1.50	48-16	6.350	11	0.05	0.8	0.9			●			
	16IR A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9			●			
	16IR G 60	1.75-3.00	14-8	9.525	16	0.12	1.2	1.7			●			
	16IR AG 60	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●	▲		
	22IR N 60	3.50-5.00	7-5	12.700	22	0.22	1.7	2.5			●			
	27IR Q 60	5.50-6.00	4.5-4	15.880	27	0.31	2.1	3.1			●			
	08UIRL U 60	1.75-2.00	14-11	4.763	8	0.10	0.9	4.0	●					
	16IRB A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9			○			
	16IRB G 60	1.75-3.00	14-8	9.525	16	0.12	1.2	1.7			●			
	16IRB AG 60	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7			●			
	06IRM A 60	0.50-1.25	48-20	3.969	6	0.05	0.5	0.6	●					
	08IRM A 60	0.50-1.50	48-16	4.763	8	0.05	0.6	0.7	●	▲	●	▲		
	11IRM A 60	0.50-1.50	48-16	6.350	11	0.05	0.8	0.9		●	●	▲		
	16IRM A 60	0.50-1.50	48-16	9.525	16	0.05	0.8	0.9		▲	●	▲		
	16IRM G 60	1.75-3.00	14-8	9.525	16	0.10	1.2	1.7		▲	●	▲		
	16IRM AG 60	0.50-3.00	48-8	9.525	16	0.05	1.2	1.7		▲	●	▲		
22IRM N 60	3.50-5.00	7-5	12.700	22	0.19	1.7	2.5		▲	●	▲			