


イグリデュールG — スリーブ型ベアリング — タイプS



- f = 0.3 ▶ d1 = 1~6
- f = 0.5 ▶ d1 = 6~12
- f = 0.8 ▶ d1 = 12~30
- f = 1.2 ▶ d1 > 30

製品番号の構成

G S M-01 03 - 02



内径d1を面取り加工
ISO 3547-1による寸法公差

製品番号	d1*	d2	b1 h13
GSM-0103-02	1.5	3.0	2.0
GSM-0203-03	2.0	3.5	3.0
GSM-02504-05	2.5	4.5	5.0
GSM-0304-03	3.0	4.5	3.0
GSM-0304-05	3.0	4.5	5.0
GSM-0304-06	3.0	4.5	6.0
GSM-0405-04	4.0	5.5	4.0
GSM-0405-06	4.0	5.5	6.0
GSM-0406-08	4.5	6.0	8.0
GSM-0407-05	4.0	7.0	5.5
GSM-0506-05	5.0	6.0	5.0
GSM-0506-07	5.0	6.0	7.0
GSM-0507-05	5.0	7.0	5.0
GSM-0507-08	5.0	7.0	8.0
GSM-0507-10	5.0	7.0	10.0
GSM-0607-06	6.0	7.0	6.0
GSM-0607-17.5	6.0	7.0	17.5
GSM-0608-015	6.0	8.0	1.5
GSM-0608-025	6.0	8.0	2.5
GSM-0608-04	6.0	8.0	4.0
GSM-0608-05	6.0	8.0	5.0
GSM-0608-055	6.0	8.0	5.5
GSM-0608-06	6.0	8.0	6.0
GSM-0608-08	6.0	8.0	8.0
GSM-0608-09	6.0	8.0	9.5
GSM-0608-10	6.0	8.0	10.0
GSM-0608-11	6.0	8.0	11.8
GSM-0608-13	6.0	8.0	13.8
GSM-0708-10	7.0	8.0	10.0
GSM-0708-19	7.0	8.0	19.0
GSM-0709-08	7.0	9.0	8.0
GSM-0709-09	7.0	9.0	9.0
GSM-0709-10	7.0	9.0	10.0
GSM-0709-12	7.0	9.0	12.0
GSM-0809-05	8.0	9.0	5.0
GSM-0809-06	8.0	9.0	6.0
GSM-0809-08	8.0	9.0	8.0
GSM-0809-12	8.0	9.0	12.0
GSM-0810-05	8.0	10.0	5.0
GSM-0810-06	8.0	10.0	6.0
GSM-0810-07	8.0	10.0	6.8
GSM-0810-08	8.0	10.0	8.0
GSM-0810-10	8.0	10.0	10.0
GSM-0810-12	8.0	10.0	12.0
GSM-0810-13	8.0	10.0	13.8
GSM-0810-15	8.0	10.0	15.0
GSM-0810-16	8.0	10.0	16.0
GSM-0810-20	8.0	10.0	20.0

製品番号	d1*	d2	b1 h13
GSM-0810-22	8.0	10.0	22.0
GSM-0911-06	9.0	11.0	6.0
GSM-1011-06	10.0	11.0	6.0
GSM-1011-10	10.0	11.0	10.0
GSM-1011-25	10.0	11.0	25.0
GSM-1011-30	10.0	11.0	30.0
GSM-1012-04	10.0	12.0	4.0
GSM-1012-045	10.0	12.0	4.5
GSM-1012-05	10.0	12.0	5.0
GSM-1012-06	10.0	12.0	6.0
GSM-1012-07	10.0	12.0	7.0
GSM-1012-08	10.0	12.0	8.0
GSM-1012-09	10.0	12.0	9.0
GSM-1012-10	10.0	12.0	10.0
GSM-1012-12	10.0	12.0	12.0
GSM-1012-14	10.0	12.0	14.0
GSM-1012-15	10.0	12.0	15.0
GSM-1012-17	10.0	12.0	17.0
GSM-1012-20	10.0	12.0	20.0
GSM-1213-12	12.0	13.0	12.0
GSM-1213-15	12.0	13.0	15.0
GSM-1214-04	12.0	14.0	4.0
GSM-1214-05	12.0	14.0	5.0
GSM-1214-06	12.0	14.0	6.0
GSM-1214-08	12.0	14.0	8.0
GSM-1214-10	12.0	14.0	10.0
GSM-1214-12	12.0	14.0	12.0
GSM-1214-14	12.0	14.0	14.0
GSM-1214-15	12.0	14.0	15.0
GSM-1214-20	12.0	14.0	20.0
GSM-1214-25	12.0	14.0	25.0
GSM-1215-06	12.0	15.0	6.0
GSM-1215-22	12.0	15.0	22.0
GSM-1216-10	12.0	16.0	10.0
GSM-1216-20	12.0	16.0	20.0
GSM-1315-070	13.0	15.0	7.0
GSM-1315-075	13.0	15.0	7.5
GSM-1315-10	13.0	15.0	10.0
GSM-1315-15	13.0	15.0	15.0
GSM-1315-20	13.0	15.0	20.0
GSM-1315-25	13.0	15.0	25.0
GSM-1416-03	14.0	16.0	3.0
GSM-1416-06	14.0	16.0	6.0
GSM-1416-08	14.0	16.0	8.0
GSM-1416-10	14.0	16.0	10.0
GSM-1416-12	14.0	16.0	12.0
GSM-1416-15	14.0	16.0	15.0
GSM-1416-20	14.0	16.0	20.0

* イグリデュールGの公差等級：E10 肉厚の公差等級=0.5mm：F9

寿命計算、CADデータ、詳しい情報は ▶ www.igus.de/jp/g

イグリデュールG

電話：03-5819-2030
FAX：03-5819-2055

